

D



C

B

A

© - TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F2	REVISED PER ECN-22-150900	22APR2022	RK	CSD



AMP WIRE RANGE	E13288 Listed
4 AWG SOLID OR STRANDED	4 AWG STRANDED P/N'S 33114 & 2-33114-1 ONLY

LR7189 Certified
4 AWG SOLID OR STRANDED P/N'S 33114 & 2-33114-1 ONLY

- 1 STAMP AMP 4W* APPROX AS SHOWN.
- 2 TIN PLATE 0.00254[.000100] MIN THK PER ASTM B545.
- 3 NICKEL PLATE 0.00762[.000300] MIN THK PER SAE AMS QQ-N-290.

D


C

33114

B

OBSOLETE	322	LOOSE PIECE, TRAY	2	170°C[338°F] MAX	2-33114-1
PRELIMINARY	100	LOOSE PIECE	3	343°C[650°F] MAX	33114-1
	100	LOOSE PIECE	2	170°C[338°F] MAX	33114
	QTY	PACKAGE TYPE	FINISH	MAX OPERATING TEMPERATURE	PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: SEE TABLE
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 16.8-26.7mm ² [33,100-52,600] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-29-93		 TE Connectivity									
		CHK DA PATTERSON 3-29-93											
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		TERMINAL, RING TONGUE, SOLISTRAND™ —							
		APVD DE MILLER 3-29-93											
		PRODUCT SPEC —		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
MATERIAL COPPER PER ASTM B-152 ANNEALED		FINISH SEE TABLE		WEIGHT —		A2		00779		C-33114			
				CUSTOMER DRAWING		SCALE		4:1		SHEET		1 of 1	

A