

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By -



LOC		DIST		REVISIONS					
AJ		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					L2	REVISED PER ECO-11-005030	11MAR11	RK	HMR

D

C


B

A



- 1 PHOSPHOR BRONZE PER QQ-B-750.
- 2 BRASS PER QQ-B-626.
- 3 ZINC PER QQ-Z-363.
- 4 POLYESTER, PBT, PER MIL-M-24519.
- 5 SILVER PLATE PER QQ-S-365
2.54 μm [.000100] MINIMUM THICK.
- 6 TIN PLATE PER ASTM-B-545
2.54 μm [.000100] MINIMUM THICK.
- 7 NICKEL PLATE PER QQ-N-290
3.81 μm [.000150] MINIMUM THICK.
- 8 GOLD PLATE PER MIL-G-45204,
0.76 μm [.000030] MINIMUM THICK.
- 9. SEE INSTRUCTION SHEET 408-9889.

DRILL HOLE TO RECEIVE
0.94±0.06 [.037±.002]
DIA PIN, 5 REQUIRED



SUGGESTED PCB CONFIGURATION

OBSOLETE	6	9-227699-0
	6	227699-3
	8	227699-2
	5	227699-1
CONTACT FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	J. LIPPERT	2-14-92	 TE Connectivity										
DIMENSIONS: INCHES			CHK	A. GABANY	2-14-92											
			APVD			J. LIPPERT	02-14-92	NAME JACK, 50 OHM, VERTICAL, PCB, BNC								
			PRODUCT SPEC			108-12078										
			APPLICATION SPEC			—										
MATERIAL			FINISH			WEIGHT	—	SIZE	A2	CAGE CODE	00779	DRAWING NO	C=227699	RESTRICTED TO	—	
1 2 3 4			5 6 7 8 9 10			CUSTOMER DRAWING			SCALE			5:1	SHEET	1 of 1	REV	L2