

TABLE I						
DASH NO	SHELL SIZE CODE - REF	A THREAD ISO METRIC	B DIA MAX	C DIA MIN	D DIA MAX	E +.008 -.000
9	A	M12 X 1 - 6H	.75	.250	.533	.044
11	B	M15 X 1 - 6H	.85	.375	.605	.044
13	C	M18 X 1 - 6H	1.00	.500	.774	.044
15	D	M22 X 1 - 6H	1.15	.625	.838	.044
17	E	M25 X 1 - 6H	1.25	.750	.963	.044
19	F	M28 X 1 - 6H	1.40	.812	1.042	.044
21	G	M31 X 1 - 6H	1.55	.937	1.217	.069
23	H	M34 X 1 - 6H	1.65	1.062	1.355	.069
25	J	M37 X 1 - 6H	1.85	1.188	1.443	.069

TABLE II		REVISIONS			
SYM	FINISH DESCRIPTION	SYM.	DESCRIPTION	DATE	APPROVED
B	CADMIUM PLATE/OLIVE DRAB	A	RELEASED	05/25/90	T.L.
C	BLACK ANODIZE	B	REVISED PER DCN 16273	06/07/00	T.L.
M	ELECTROLESS NICKEL	C	REVISED PER DCN 21859	01/15/04	T.L.
NF	CAD/O. D. OVER ELECTROLESS NICKEL (1000 HOUR SALT SPRAY)	D	REVISED PER DCN 25640	04/22/06	T.L.

PART NUMBER DEVELOPMENT


EXAMPLE: GS85049/69 - 11 NF D

BASIC PART NO

SHELL SIZE, TABLE I

FINISH SYM, TABLE II

D = DRAIN HOLES
OMIT FOR NONE



- NOTES:
- 1. ASSEMBLY IDENTIFIED WITH MANUFACTURER'S NAME AND P/N, SPACE PERMITTING.
 - 2. GLENAIR 600 SERIES BACKSHELL ASSEMBLY TOOLS ARE RECOMMENDED FOR ASSEMBLY AND INSULATION.
 - 3 ADAPTER WITH DRAIN HOLES NOT SUPPLIED WITH O-RING.
 - 4. MATERIAL/FINISH:
ADAPTER, COUPLING NUT - AL ALLOY/SEE TABLE II
O-RING - SILICONE/N.A.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONS ± 1/16 DECIMALS .XX ± .03 .XXX ± .015 ANGLES ± 2°		DRAWN	T.L.E	05/24/90	GLENAIR, INC. CAD 1990 ° 1211 AIR WAY - GLENDALE - CALIFORNIA 91201	
		CHECK	P.OAKES	05/24/90		
		ENGR	G.BURGE	05/24/90	ADAPTER, SHRINK BOOT, FOR MIL-DTL-38999, SERIES III & IV CONNECTORS	
		<i>R. P. Oaks</i> APPROVED				
DO NOT SCALE THIS DRAWING		<i>P.D. Oaks</i> APPROVED			CODE IDENT. NO.	SIZE
		RELEASE DATE 05/25/90				
B/F 90-2689	P/C 31	NON REPARABLE COMMERCIAL ITEM			06324	C
		SCALE N/A		WEIGHT N/A	GS85049/69	
				SHEET 1 OF 1	REV. D	