

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19





BY AMP INCORPORATED. ALL RIGHTS RESERVED.

CAD
DO NOT REVISE
EXCEPT BY CADLOC
APDIST
—

REVISIONS

REVISÃO

P	LTR LT	DESCRIPTION DESCRIÇÃO	DATE DATA	DWN DES	APVD APR
	F	REVISED BY ECLB0015/04	13APR04	AP	PLF
	F1	REVISED PER ECO-09-026444	NOV09	KK	AEQ

SECÇÃO A-A
SECTION A-ASECÇÃO B-B
SECTION B-B

NOTE:

1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

WIRE RANGE 1,0 - 2,5 mm2	INSULATION RANGE ø 2,3- 3,5 mm	ESTANHADO / TIN PLATED ---/---	LATÃO / BRASS LATÃO / BRASS	1 626500-2 626500-1
THIS DRAWING IS A CONTROLLED DOCUMENT.		ACABAMENTO / FINISH	MATERIAL	PART NUMBER
DIMENSIONS: DIMENSÕES MM	TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERÂNCIA NCO ESPECIFICADAS	DWN/DES A.PERUSSI CHK/CH P.L.FARIA APVD/APR L.W.PRADO	NAME DESENHO	AMP do BRASIL Ltda. São Paulo - Brasil
	0 PLC/DEC ± - 1 PLC/DEC ± 0,3 2 PLC/DEC ± - 3 PLC/DEC ± - 4 PLC/DEC ± - ANGLES/ANGULARES ± 1°	PRODUCT SPEC —	SIZE 114-37000	RESTRICTED TO —
MATERIAL	FINISH ACABAMENTO SEE TABLE	WEIGHT —	CAGE CODE A3 00779	DRAWING NO DESENHO NO 626500
CUSTOMER DRAWING/DESENHO DE CLIENTE			SCALE ESCALA 5:1	SHEET FOLHA 1 OF 1
			REV F1	