





AS SHOWN : -1, -3, 1--2, 2--1, 2--3, 4--1, 5--1,
5--3, 6--2, 6--4, 7--1, 7--3, 9--1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED	11NOV2021	M.T	H.T

PLATING	PACKAGING	SCREW INCLUSION	$\triangle 4$ DIM A	$\triangle 3$ DIM B (HOST BOARD THICKNESS)	$\triangle 4$ DIM D	PARTS No.
0.76 μ m Au	SOFT TRAY	YES	0	1.57 ± 0.15	1.22	2340324-1
		NO	0	1.57 ± 0.15	1.22	2340324-3
		YES	0.3	1.93 ± 0.19	1.58	1-2340324-2
		YES	0	2.36 ± 0.23	1.97	2-2340324-1
		NO	0	2.36 ± 0.23	1.97	2-2340324-3
		YES	0	$2.55^{+0.23}_{-2.6}$, $2.6^{+0.23}_{-2.6}$	2.15	4-2340324-1
	HARD TRAY	YES	0	1.57 ± 0.15	1.22	5-2340324-1
		NO	0	1.57 ± 0.15	1.22	5-2340324-3
		YES	0.3	1.93 ± 0.19	1.58	6-2340324-2
		NO	0.3	1.93 ± 0.19	1.58	6-2340324-4
		YES	0	2.36 ± 0.23	1.97	7-2340324-1
		NO	0	2.36 ± 0.23	1.97	7-2340324-3
		YES	0	$2.55^{+0.23}_{-2.6}$, $2.6^{+0.23}_{-2.6}$	2.15	9-2340324-1

119			THIS DRAWING IS A CONTROLLED DOCUMENT.		M.TANAKA CHK30JUL2018		TE Connectivity Ltd.					
2M2 SCREW			DIMENSIONS: mm  TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3 Ø-PLC +1-PLC -2-PLC -3-PLC +4-PLC ANGLES ± ± ± ± ± ±		J.TSUJI		NAME					
2M2 NUT PLATE					APVD		30JUL2018					
4COVER HOUSING 28P					K.KOBAYASHI		140 POSITION					
2COVER HOUSING 14P					PRODUCT SPEC		SLIVER 2.0 STRADDLE MOUNT					
1HOUSING					APPLICATION SPEC		108-140197					
140CONTACT			MATERIAL		FINISH		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
QTYNAMEITEM No.			1		2		114-78033		A200779		C=2340324	
CUSTOMER DRAWING					WEIGHT		SCALE		SHEET		REV	
							4:1		1 of 5		F	

D

C

B



A

D

C

B

A



HOST BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

±0.3

9-PLC ±

4-PLC ±

3-PLC ±

2-PLC ±

1-PLC ±

0-PLC ±

ANGLES ±

FINISH

MATERIAL

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity Ltd.

NAME

140 POSITION SLIVER 2.0 STRADDLE MOUNT

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=2340324

SCALE


4:1

SHEET

2 of 5

REV

F



4

3

2

1

© - TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

CONNECTOR CONTACT IDENTIFICATION

5

6

CONTACT NUMBER	SIDE A	SIDE B
1	GROUND	GROUND
2	SIGNAL	SIGNAL
3	SIGNAL	SIGNAL
4	GROUND	GROUND
5	SIGNAL	SIGNAL
6	SIGNAL	SIGNAL
7	GROUND	GROUND
8	SIGNAL	SIGNAL
9	SIGNAL	SIGNAL
10	GROUND	GROUND
11	SIGNAL	SIGNAL
12	SIGNAL	SIGNAL
13	GROUND	GROUND
14	SIGNAL	SIGNAL
15	SIGNAL	SIGNAL
16	GROUND	GROUND
17	SIGNAL	SIGNAL
18	SIGNAL	SIGNAL
19	GROUND	GROUND
20	SIGNAL	SIGNAL
21	SIGNAL	SIGNAL
22	GROUND	GROUND
23	SIGNAL	SIGNAL
24	SIGNAL	SIGNAL
25	GROUND	GROUND
26	SIGNAL	SIGNAL
27	SIGNAL	SIGNAL
28	GROUND	GROUND
29	GROUND	GROUND
30	SIGNAL	SIGNAL
31	SIGNAL	SIGNAL
32	GROUND	GROUND
33	SIGNAL	SIGNAL
34	SIGNAL	SIGNAL
35	GROUND	GROUND

CONTACT NUMBER	SIDE A	SIDE B
36	SIGNAL	SIGNAL
37	SIGNAL	SIGNAL
38	GROUND	GROUND
39	SIGNAL	SIGNAL
40	SIGNAL	SIGNAL
41	GROUND	GROUND
42	GROUND	GROUND
43	GROUND	GROUND
44	SIGNAL	SIGNAL
45	SIGNAL	SIGNAL
46	GROUND	GROUND
47	SIGNAL	SIGNAL
48	SIGNAL	SIGNAL
49	GROUND	GROUND
50	SIGNAL	SIGNAL
51	SIGNAL	SIGNAL
52	GROUND	GROUND
53	SIGNAL	SIGNAL
54	SIGNAL	SIGNAL
55	GROUND	GROUND
56	SIGNAL	SIGNAL
57	SIGNAL	SIGNAL
58	GROUND	GROUND
59	SIGNAL	SIGNAL
60	SIGNAL	SIGNAL
61	GROUND	GROUND
62	SIGNAL	SIGNAL
63	SIGNAL	SIGNAL
64	GROUND	GROUND
65	SIGNAL	SIGNAL
66	SIGNAL	SIGNAL
67	GROUND	GROUND
68	SIGNAL	SIGNAL
69	SIGNAL	SIGNAL
70	GROUND	GROUND

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0-PLG

1-PLG

2-PLG

3-PLG

4-PLG

ANGLES

FINISH

TOLERANCES UNLESS OTHERWISE SPECIFIED:

+

-

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

140 POSITION
SLIVER 2.0 STRADDLE MOUNT

A200779

C=2340324

SCALE

NTS

SHEET

4 of 5

REV

F

TE

TE Connectivity Ltd.

1471-9 (1/15)



HARD TRAY PACKAGING: 5--1, 6--2, 7--1
5--3, 6--4, 7--3, 9--1

1. MATERIAL: HIPS, COLOR: BLACK
2. QTY. : 6 X 5 = 30 POCKETS PER TRAY
③ MARKING
4. TOLERANCES ON TRAY DIMENSIONS ARE REFERENCE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CHK APVD PRODUCT SPEC APPLICATION SPEC WEIGHT		 TE Connectivity Ltd.	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0-PLC ± 1-PLC ± 2-PLC ± 3-PLC ± 4-PLC ± ANGLES ± MATERIAL FINISH		NAME 140 POSITION SLIVER 2.0 STRADDLE MOUNT	
		SIZE A2		CAGE CODE 00779	
		DRAWING NO C=2340324		RESTRICTED TO /	
		CUSTOMER DRAWING		SCALE NTS	
		SHEET 5 of 5		REV F	