


THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2005, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED INPUT POWER	1	W
MAX INPUT POWER	1.5	W
IMPEDANCE	8±15%	OHM
OUTPUT SPL @ 0.1W/0.1M (AT 0.8, 1.0, 1.2, 1.5 kHz)	91±3	dBA
DISTORTION (MAX.)	5%	—
RESONANT FREQUENCY	500±20%	Hz
FREQUENCY RANGE	Fo ~ 4,500	Hz
HOUSING MATERIAL	METAL	—
CONE MATERIAL	MYLAR	—
MAGNET MATERIAL	NdFeB	—
OPERATING TEMPERATURE	-30 ~ +60	°C
WEIGHT	12	grams

REVISIONS


LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	1/30/20	



NOTES:

- ALL DIMENSIONS ARE IN MILLIMETERS.
- SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
- THIS PART IS RoHS 2011/65/EU COMPLIANT.

UNLESS OTHERWISE SPECIFIED:
ALL PURCHASES ARE SUBJECT TO THE PUI AUDIO
TERMS AND CONDITIONS SALE FOUND AT
http://www.puiaudio.com/pdf/terms_conditions.pdf
(paper copy available upon request).
DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE
 ± 0.5 AND ANGLES ARE $\pm 3^\circ$.



3541 Stop Eight Road
Dayton, Ohio 45414

BASE SPEAKER:
AS03608MR-R
FILE NAME
AS03608MR-LW100-R.D

APPROVALS	DATE
DRAWN M. V.	1/20
CHECKED M. V.	1/20
APPROVED B. R.	1/20

SPEAKER	
SIZE A	DRAWING NO. AS03608MR-LW100-R
SCALE: N.T.S.	SHEET 1 OF 1