




Series 206RA

Right Angle Panel DIP Switch

- Designed for panel applications, saves cost of right angle socket
- Available as SPST, SPDT, DPST, 3PST
- Optional tape seal for board spray washing
- Available with low profile, standard, or extended actuators
- Gold Plated Contacts



Description

The terminals are molded into the thermoset base and provide an electrostatic discharge shield rating to 22KV when the front row of terminals are connected to ground. The optimized gold plated contact design incorporates a dimple-to-flat surface wiping interface for long-term contact corrosion resistance, making the 206RA an ideal choice for many applications.

Ordering Information

Series	Number of Poles	Number of Throws	Number of Switch Positions	Type of Terminals	Actuator Height	Bottom Epoxy Seal	Top Tape Seal	Actuation Preset																																																					
206 -	1	2	1	RA	LP	S	T	N																																																					
<table><tr><th>Code</th><th>No. of poles</th></tr><tr><td>Blank</td><td>For SPST</td></tr><tr><td>1</td><td>Single pole</td></tr><tr><td>2</td><td>Double poles</td></tr><tr><td>3</td><td>3 poles</td></tr></table>		Code	No. of poles	Blank	For SPST	1	Single pole	2	Double poles	3	3 poles	<table><tr><th>Code</th><th>No. of switch positions</th></tr><tr><td>1</td><td>1 position (Not available for SPST)</td></tr><tr><td>2</td><td>2 positions</td></tr><tr><td>3</td><td>3 positions</td></tr><tr><td>4</td><td>4 positions</td></tr><tr><td>5</td><td>5 positions</td></tr><tr><td>6</td><td>6 positions</td></tr><tr><td>7</td><td>7 positions</td></tr><tr><td>8</td><td>8 positions</td></tr><tr><td>9</td><td>9 positions</td></tr><tr><td>10</td><td>10 positions</td></tr><tr><td>12</td><td>12 positions</td></tr></table>		Code	No. of switch positions	1	1 position (Not available for SPST)	2	2 positions	3	3 positions	4	4 positions	5	5 positions	6	6 positions	7	7 positions	8	8 positions	9	9 positions	10	10 positions	12	12 positions	<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>RA</td><td>Right Angle</td></tr></table>		Code	Spec.	RA	Right Angle	<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>Blank</td><td>Standard (0.89mm/.035")</td></tr><tr><td>E</td><td>Extended (3.43mm/.135") (SPST only)</td></tr><tr><td>LP</td><td>Low profile (Flush) (SPST&SPDT only)</td></tr></table>		Code	Spec.	Blank	Standard (0.89mm/.035")	E	Extended (3.43mm/.135") (SPST only)	LP	Low profile (Flush) (SPST&SPDT only)	<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>Blank</td><td>Ship at OFF position (SPST, DPST&3PST only)</td></tr><tr><td>N</td><td>Ship at ON position (SPST, DPST&3PST only)</td></tr></table>		Code	Spec.	Blank	Ship at OFF position (SPST, DPST&3PST only)	N	Ship at ON position (SPST, DPST&3PST only)
Code	No. of poles																																																												
Blank	For SPST																																																												
1	Single pole																																																												
2	Double poles																																																												
3	3 poles																																																												
Code	No. of switch positions																																																												
1	1 position (Not available for SPST)																																																												
2	2 positions																																																												
3	3 positions																																																												
4	4 positions																																																												
5	5 positions																																																												
6	6 positions																																																												
7	7 positions																																																												
8	8 positions																																																												
9	9 positions																																																												
10	10 positions																																																												
12	12 positions																																																												
Code	Spec.																																																												
RA	Right Angle																																																												
Code	Spec.																																																												
Blank	Standard (0.89mm/.035")																																																												
E	Extended (3.43mm/.135") (SPST only)																																																												
LP	Low profile (Flush) (SPST&SPDT only)																																																												
Code	Spec.																																																												
Blank	Ship at OFF position (SPST, DPST&3PST only)																																																												
N	Ship at ON position (SPST, DPST&3PST only)																																																												
<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>Blank</td><td>For SPST</td></tr><tr><td>1</td><td>Single throw</td></tr><tr><td>2</td><td>Double throws (Single pole only)</td></tr></table>		Code	Spec.	Blank	For SPST	1	Single throw	2	Double throws (Single pole only)			<table><tr><th>Code</th><th>Bottom epoxy seal</th></tr><tr><td>Blank</td><td>No epoxy seal</td></tr><tr><td>S</td><td>Epoxy seal</td></tr></table>		Code	Bottom epoxy seal	Blank	No epoxy seal	S	Epoxy seal	<table><tr><th>Code</th><th>Top tape seal</th></tr><tr><td>Blank</td><td>No top tape seal</td></tr><tr><td>T</td><td>Top tape seal for Board spray washing (Not available for extended actuator)</td></tr></table>		Code	Top tape seal	Blank	No top tape seal	T	Top tape seal for Board spray washing (Not available for extended actuator)																																		
Code	Spec.																																																												
Blank	For SPST																																																												
1	Single throw																																																												
2	Double throws (Single pole only)																																																												
Code	Bottom epoxy seal																																																												
Blank	No epoxy seal																																																												
S	Epoxy seal																																																												
Code	Top tape seal																																																												
Blank	No top tape seal																																																												
T	Top tape seal for Board spray washing (Not available for extended actuator)																																																												



Electrical Specifications


Parameter	Conditions & Remarks	Min	Max	Unit
Circuit	SPST	2	12	position
	SPDT	1	6	
	DPST	1	6	
	3PST	1	4	
Contact Resistance	Initial		50	milliohms
	At end of life		100	
Insulation Resistance	Between insulated terminals	1000		megohms
Dielectric Strength	500 VAC between adjacent switches		1	minute
Switch Capacitance	Between adjacent closed switches		5.0	pF
Nonswitching Rating			100 or 50	mA or VDC

Mechanical and Environmental

Actuation Life	10,000 cycles switching 50mA @ 24 VDC
Soldering	Maximum wave temperature, 260°C for 5 seconds
MSL	Level 1
RoHS	Lead-Free. Fully compliant to RoHS Directive 2011/65/EU and 2015/863/EU
Shock	Per MIL-STD-202F, method 213B, condition A(50G's) with no contact inconsistencies greater than 1 microsecond
Vibration	Per MIL-STD-202F, method 204D, condition B (.06" or 15G's between 10 HZ to 2K HZ) with no contact inconsistencies greater than 1 microsecond
Seal	Bottom epoxy seal optional Tape seal optional
Marking	Special side or top marking available-consult CTS
Packaging:	Standard anti-static tube packaging
Operating Temperature Range	-55°C to +85°C
Storage Temperature Range	-40°C to +85°C

Mechanical Specifications

Figure 1 – SPST



DIMENSION : $\frac{\text{mm}}{\text{inch}}$

STANDARD TOLERANCE FOR ALL STYLES :

$$.X \text{ (1 PLACE): } \frac{\pm 0.3}{\pm .012} \quad XX(2 \text{ PLACE}): \frac{\pm 0.13}{\pm .005}$$



Please find switch body dimensions of 206RA DIP switches with SPDT, DPST, 3PST circuitry on the 206 series data sheet.

Standard Part #							
Dimensions	SPST Switches		SPDT&DPST Switches			3PST Switches	
"A" Overall (mm/inch)	No of SW positions	SPST P/N	No of SW positions	SPDT P/N	DPST P/N	No of SW positions	3PST P/N
7.26 / .286	2	206- 2RA	1	206-121RA	206-211RA	—	—
9.80 / .386	3	206- 3RA	—	—	—	1	206-311RA
12.34 / .486	4	206- 4RA	2	206-122RA	206-212RA	—	—
14.88 / .586	5	206- 5RA	—	—	—	—	—
17.42 / .686	6	206- 6RA	3	206-123RA	206-213RA	2	206-312RA
19.96 / .786	7	206- 7RA	—	—	—	—	—
22.50 / .886	8	206- 8RA	4	206-124RA	206-214RA	—	—
25.04 / .986	9	206- 9RA	—	—	—	3	206-313RA
27.58 / 1.086	10	206-10RA	5	206-125RA	206-215RA	—	—
32.66 / 1.286	12	206-12RA	6	206-126RA	206-216RA	4	206-314RA