




D



SINGLE LATCH DETAIL FOR
2323743-8 AND 1-2323743-0





SINGLE LATCH DETAIL FOR
1-2323743-2 THRU 1-2323743-6

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FIRST RELEASED	16AUG2019	WH	DZ


NOTES:

1. MATERIAL: NYLON 66, UL94V-0, COLOR:NATURAL.
2. DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
3. RECOMMENDED MATING CAP:[]-2323745-[] AND []-2324201-[]
HEADER:[]-2323245-[], []-2323751-[] AND []-2323750-[]
4. THE HOUSING ACCEPTS TERMINALS : 2110989-1 OR 2232905-1
1744423-1 OR 2232983-1
5. ACCEPT OPTIONAL TPA: []-1969443-[] OR []-1969825-[]
6. COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30(GWT)


C



B



DUAL LATCH DETAIL FOR
1-2323743-8 THRU 4-2323743-0



2-2323743-0 SHOWN

1.25	47.50	51.04	40	4-2323743-0
0.00	45.00	48.54	38	3-2323743-8
1.25	42.50	46.04	36	3-2323743-6
0.00	40.00	43.54	34	3-2323743-4
1.25	37.50	41.04	32	3-2323743-2
0.00	35.00	38.54	30	3-2323743-0
1.25	32.50	36.04	28	2-2323743-8
0.00	30.00	33.54	26	2-2323743-6
1.25	27.50	31.04	24	2-2323743-4
0.00	25.00	28.54	22	2-2323743-2
1.25	22.50	26.04	20	2-2323743-0
0.00	20.00	23.54	18	1-2323743-8
1.25	17.50	21.04	16	1-2323743-6
0.00	15.00	18.54	14	1-2323743-4
1.25	12.50	16.04	12	1-2323743-2
0.00	10.00	13.54	10	1-2323743-0
1.25	7.50	11.04	8	2323743-8
DIM M		DIM N	DIM L	POSITION
				PART NO.

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±0.25
3 PLC ±
4 PLC ±
ANGLES ±5°
FINISH

MATERIAL

DWN 26AUG2018
CHK 27AUG2018
APVD 27AUG2018

WARREN HUO
DANIEL ZHANG
DANIEL ZHANG

PRODUCT SPEC
108-106357
APPLICATION SPEC
114-13315
WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
PLUG HOUSING, EP 2.5 DUAL ROW
WTW AND WTB, GWT

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2323743

RESTRICTED TO
-

SCALE
N/A

SHEET
1

OF
1

REV
A