

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC
F

DIST
00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
B		HOLE DIA. TOLERANCES	09JUN2006	JJD	YP
C		ECR 07-025006	29OCT2007	JT	GR

COUPE C - C



6MAX

STAMP : AMP 12-10*

1.5MAX

FOR INSULATION
Ø2.60 - 5.44
Ø7.40 MAX


SLEEVE

INSULATION

SERRATIONS

BODY 0.98±0.05 TONGUE
THICKNESS

Ø8.34±0.13
FOR 5/16 OR M8 STUD



SCALE 2:1

13.49±0.15

0.79 MIN

11.56 MIN

27.69 MAX

34.50MAX

WIRE
TERMINAL

1577649-1

BODY : COPPER ANNEALED
FINISH : NICKEL PLATED

SLEEVE : COPPER ANNEALED
FINISH : NICKEL PLATED

INSULATION : PEEK
COLOR : BLACK


DESCRIPTION

PART NUMBER

MATERIAL & FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.3
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±5
FINISH

MATERIAL SEE TABLE

SEE TABLE

DWN 27FEB2006

CHK JJ. DESPRETZ 27FEB2006

APVD G-ROBERT 27FEB2006

Y-PETRONIN

PRODUCT SPEC

108-15356

APPLICATION SPEC

114-15102

WEIGHT 2,9 gr

CUSTOMER DRAWING

tyco
Electronics

Tyco Electronics France SAS
95300 Pontoise, France

NAME
TERMINAL, PEEK PIDG STRATO,
10 AWG

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779C-1577649

SCALE 5:1 SHEET 1 OF 1 REV C