







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

AMP WIRE RANGE	 LR7189 Certified
SEE TABLE STRANDED	WIRE SIZE PER TABLE STRANDED



- 1 STAMP AMP  APPROX AS SHOWN
SEE TABLE BELOW.
- 2 WIRE INSULATION DIA: 0.965–2.794[.038–.110] FOR 22 AWG
1.168–2.794[.046–.110] FOR 20 AWG
1.422–2.794[.056–.110] FOR 18 AWG
- 3 BODY MATERIAL THK: 0.787±0.051[.031±.002].
- 4 APPLIES FROM EDGE OF METAL WIRE BARREL
TO CENTER OF STUD HOLE.
- 5 CSA CERTIFIED

5	M7928/1-37 CLASS 1	WHITE	18*	18	1000	LOOSE PIECE	2-328975-3
5	M7928/1-28 CLASS 1	RED	20*	20	1000	LOOSE PIECE	2-328975-2
5	M7928/1-19 CLASS 1	GREEN	22*	22	1000	LOOSE PIECE	2-328975-1
	MILITARY P/N AND CLASS	STRIPE COLOR	1STAMPING	WIRE SIZE	QUANTITY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE: 105°C[221°F] MAX

VOLTAGE RATING: 300 V MAX

WIRE RANGE:

CIRC MIL AREA

22 0.38mm² [754]


20 0.60mm² [1,186]

18 0.96mm² [1,900]

STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]



MATERIAL
BODY & SLEEVE
COPPER PER ASTM B-152
INSULATION: NYLON

FINISH

BODY & SLEEVE
TIN PLATE
PER ASTM B545
INSULATION: COLOR-RED

DWN DK SCHRUM 9/8/93

CHK RE HERSEY 9/8/93

APVD ML ELLIS 9/8/93

PRODUCT SPEC

APPLICATION SPEC

114-2157

WEIGHT -

CUSTOMER DRAWING

 TE Connectivity Ltd.

NAME
TERMINAL, RING TONGUE, PIDG™,
WIRE SIZE, 22, 20 & 18 AWG

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-328975

SCALE NTS

SHEET 2 OF 2

REV P2