









SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	NONE	ON
2-3, 5-6	OPEN	2-1, 5-4



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERMINAL NUMBERS FOR REF ONLY
- ▲4. PLATING MATERIAL: GOLD
- RATING: 0.4 VOLT-AMPS (VA) MAX. @20V MAX. AC OR DC
- ELECTRIC LIFE: 40,000 make-and-break cycles at full load.
- INSULATION RESISTANCE: 1,000 Mega-ohm min.
- DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
- OPERATING TEMP.: -30°C to 85°C
- ▲ DENOTES CRITICAL PARAMETER.
- 2002/95/EC (ROHS) COMPLIANT



ISOMETRIC

D	17324	FIXED ACT, AND BUSHING DIMS.	5/24/07	TN
C	17297	ADDED NEW LOGO	5/16/07	TN
B	17038	FIXED ACT. LENGTH, NOTES	2/27/07	TN
A	14238	RELEASED FOR PRODUCTION	8/17/04	TN
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE 100DP1T9B1M7RE

SCALE 2:1

DATE 5/24/2007

DR TN

DWG T121074

REV D