





DRAWING FOR REFERENCE: This is subject to change without notice
08/11/2012





- NOTE 1. ALL LEADS CO-PLANARITY SHALL BE 0.1 MAX.
2. PER REEL : 8000 CONNECTORS.
3. AT THE BEGINNING OF THE REEL, 100 mm AT MIN SHALL BE EMPTY POCKETS.
AT THE END OF THE REEL, 160 mm AT MIN SHALL BE EMPTY.
4. CONTACT PLATING SPECIFICATIONS.
CONTACT AREA : GOLD 0.1μm MIN.
SMT LEAD : GOLD 0.05μm MIN.
UNDERPLATING : NICKEL 1μm MIN.
(SURFACE : SEALING)
5. METAL HOLD DOWN PLATING SPECIFICATIONS.
MOUNTING AREA: GOLD 0.05μm MIN.
UNDERPLATING : NICKEL 1μm MIN.
6. PEEL FORCE OF COVER TAPE REFERS TO JIS C 0806.

RECOMMENDED METAL MASK OPENING PATTERN




RECOMMENDED SOLDER PASTE THICKNESS : 120μm

RECOMMENDED PATTERN



ENGAGEMENT FIGURE



3	PHOSPHOR BRONZE	5	6	PS	PLASTIC REEL(BLACK)
2	PHOSPHOR BRONZE	4	5	POLYESTER	CLEAR(TOP COVER TAPE)
1	LCP	UL94V-0, BLACK	4	PS	CLEAR(EMBOSSED COVER TAPE)
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	
HIROSE ELECTRIC CO., LTD.		APPROVED : KH. IKEDA	10.11.23	DRAWING NO.	EDC3-308589-06
		CHECED : TS. MIYAZAKI	10.11.22	PART NO.	DF37B-70DP-0.4V(75)
		DESIGNED : RT. SHIMIZU	10.11.22	CODE NO.	CL684-3014-4-75
		DRAWN : YN. SAKAMOTO	10.11.19		
		DESIGNED	CHECKED	DATE	

DRAWING FOR REFERENCE: This is subject to change without notice
08/11/2012

