




| ▲ SWITCH FUNCTION |        |        |
|-------------------|--------|--------|
| POS. 1            | POS. 2 | POS. 3 |
|                   |        |        |
| (ON)              | OFF    | (ON)   |
| 2-3               | OPEN   | 2-1    |

( ) = MOMENTARY



## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. PLATING MATERIAL: GOLD
5. RATING: 0.4VOLT-AMPS MAX. @20V AC OR DC MAX.
6. ELECTRIC LIFE: 40,000 make-and-break cycles at full load.
7. INSULATION RESISTANCE: 1,000 M $\Omega$  min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @ sea level
9. OPERATING TEMP.: -30°C to 85°C
10. ▲ DENOTES CRITICAL PARAMETER.

▲ ACTUATOR  
COLOR: BLACK

| REV | ECO NO     | DESCRIPTION | DATE     | BY | E-SWITCH®             |           |    |         | OBJECT ID |
|-----|------------|-------------|----------|----|-----------------------|-----------|----|---------|-----------|
| A   | ECO-100610 | Release     | 12/14/21 | MW | TITLE 300SP4J1BLKM2RE |           |    |         | 100120248 |
|     |            |             |          |    | SCALE                 | DATE      | DR | DWG     | REV       |
|     |            |             |          |    | 2:1                   | 12/9/2021 | MW | T314045 | A         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO  
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED