



SPECIFICATIONS		
PARAMETERS	VALUES	UNITS
RESONANT FREQUENCY	2,800 ± 500	Hz
RESONANT IMPEDANCE (MAX)	300	Ohm
MAX INPUT VOLTAGE	30	Vp-p
CAPACITANCE @ 100 HZ	30,000 ±30%	pF
PLATE MATERIAL	BRASS	-
OPERATING TEMPERATURE	-20 ~ +60	°C
STORAGE TEMPERATURE	-20 ~ +70	°C

REVISION HISTORY			
LTR	DESCRIPTION	DATE	APPROVED
-	RELEASED FROM ENGINEERING	6/5/2003	
A	REVISED TO NEW TEMPLATE	9/4/2003	R.W.
B	REVISED SPECIFICATIONS	1/15/2004	R.W.
C	REVISED DIMENSIONS	10/29/2004	R.W.
D	REVISED DIMENSION SIZE AND STYLE	1/25/2006	B.R.
E	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	8/13/2010	B.R.
F	REVISED CAPACITANCE FREQUENCY	2/12/2020	M.V.



UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.	SIZE A3	Designed by	Date	Checked by	Date	Approved by	Date	Drawn Date	
		B.C.I.	6/5/2003			S.J.	6/5/2003	8/13/2010	
					AB3528B				
AB3528B.idw				Bender				Edition -	Sheet 1 / 1