




SQUARE FLANGE JACK RECEPTACLE WITH TAB CONTACT

R185.403.490


Series : 7/16



PANEL CUT OUT		
A DIA		
B DIA		
4 holes		
	mm	
	Maxi	mini
A	12.3	12.1
B	3.8	3.7
C	24.8	24.7



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
BODY	BRASS	BBR 0.5 OVER SILVER 3
CENTER CONTACT	BRONZE	SILVER 5 PASSIVATED OVER COPPER 0.5
OUTER CONTACT	BRASS	SILVER 5 PASSIVATED OVER COPPER 0.5
INSULATOR	PTFE	
GASKET		
OTHERS PARTS		
-	-	-
-	-	-

Issue : 0938 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RADIAL

SQUARE FLANGE JACK RECEPTACLE
WITH TAB CONTACT

R185.403.490

Series : 7/16

PACKAGING

Standard	Unit	Other
20	'W' option	Contact us

SPECIFICATION

ELECTRICAL CHARACTERISTICS

Impedance	50	Ω
Frequency	0-7.5	GHz
VSWR	**1.3 + 0.0000	x F(GHz) Maxi
Insertion loss	*0.05	$\sqrt{F}(\text{GHz})$ dB Maxi
RF leakage	- (NA	- F(GHz)) dB Maxi
Voltage rating	1400	Veff Maxi
Dielectric withstanding voltage	4000	Veff mini
Insulation resistance	10000	M Ω mini

ENVIRONMENTAL

Operating temperature	-55/+120	$^{\circ}\text{C}$
Hermetic seal	NA	Atm.cm3/s
Panel leakage	NA	

OTHER CHARACTERISTICS

Assembly instruction **NA**

Others :

**Interface only(VSWR 4-7.5)

VSWR(0-4GHz) :1.02+0.02F(GHz)max

*Insertion loss(0-4GHz)

MECHANICAL CHARACTERISTICS

Center contact retention	
Axial force – Mating end	200 N mini
Axial force – Opposite end	40 N mini
Torque	25 N.cm mini
Recommended torque	
Mating	NA N.cm
Panel nut	NA N.cm
Mating life	500 Cycles mini
Weight	83.5680 g

Issue : 0938 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RADIAL 