




COIL: @ 25°C
 RESISTANCE 1560 OHMS $\pm 10\%$
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE VOLTAGE 14.2 VDC
 TURN-ON BASE CURRENT 0.13 mADC
 MUST RELEASE 8.0 VDC MAX, 1.37 VDC MIN.

ENVIRONMENT:


VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: TURN-ON TIME 2.0 MS MAX
 TURN-OFF TIME 7.5 MS MAX
 CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 3/17/97 CK *[Signature]* 3/17/97

**COMMUNICATIONS
 INSTRUMENTS, INC.**

JMACT-26XL

CUST. QPL
 CUST. NO. M28776/1-030L

TYPE JMA RELAY