

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD

E

REV / 0720-0778-95


100CT95

MLE

NB

AMP
WIRE RANGE

E13288

LR7189
Certified12-10 AWG
SOLID OR STRANDED12-10 AWG
SOLID OR STRANDED12-10 AWG
SOLID OR STRANDED

1 STAMP AMP 12-10* APPROX AS SHOWN

2. WIRE INSUL DIA, 4.32-7.62 [.170-.300]


3. TONGUE MATERIAL THK, 1.02±0.05
[.040±.002]

---	-----	-----
---	-----	-----
500	LOOSE PIECE	35604
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMMAX RECOMMENDED OPERATING
TEMPERATURE:
105° C [221° F]THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm [in]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ±-
1 PLC ±-
2 PLC ±0.20 [.008]
3 PLC ±-
4 PLC ±-
ANGLES ±-MATERIAL
BODY, SLV, COPPER PER ASTM B 152
INSUL, PVC, COLOR, YELLOWFINISH
BODY & SLV, TIN PLATE
PER MIL-T-10727DWN
M ELLIS

17APR95

CHK
C PRESNELL

17APR95

APVD
N BIRCH

17APR95

PRODUCT SPEC

UL 486A

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

AMPAMP Incorporated
Harrisburg, PA 17105-3608

NAME

TERMINAL, RING TONGUE, PIDG™,
WIRE SIZE, 12-10 AWG

SIZE

CAGE CODE

DRAWING NO

A3

00779

C-35604

SCALE 4:1

SHEET

1 OF 1

REV E