

**BCZ 3.81/20/180 SN BK BX****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Product image**

Similar to illustration

Female socket connectors with clamping-yoke screw system for connecting wires.

Three wire-outlet directions are available and provide flexible connection-level design options:

- 180° wire parallel to plugging direction
- 90° wire perpendicular and above plugging direction
- 270° wire perpendicular and below plugging direction

There are three housing shapes, covering many different requirements, to choose from:

- Standard housing without flange
- Flange with screw (F)
- Flange featuring Weidmüller's patented release latch (LR) for lock-and-release latching with no strain and no tools needed.

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of customary connectors and offer space for labelling and coding.

**General ordering data**

|              |                                                                                                                                       |
|--------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, female plug, 3.81 mm, Number of poles: 20, 180°, Clamping yoke connection, Clamping range, max. : 1.5 mm², Box |
| Order No.    | <a href="#">1941000000</a>                                                                                                            |
| Type         | BCZ 3.81/20/180 SN BK BX                                                                                                              |
| GTIN (EAN)   | 4032248655847                                                                                                                         |
| Qty.         | 50 pc(s).                                                                                                                             |
| Product data | IEC: 320 V / 17.5 A / 0.2 - 1.5 mm²<br>UL: 300 V / 10 A / AWG 28 - AWG 16                                                             |
| Packaging    | Box                                                                                                                                   |

**BCZ 3.81/20/180 SN BK BX****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 16.1 mm  | Depth (inches)  | 0.634 inch |
| Height     | 11.1 mm  | Height (inches) | 0.437 inch |
| Width      | 76.29 mm | Width (inches)  | 3.004 inch |
| Net weight | 15.76 g  |                 |            |

**Environmental Product Compliance**

|            |                |      |                                      |
|------------|----------------|------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 | SCIP | ea9dd4b8-c51f-409c-885a-41700372be61 |
|------------|----------------|------|--------------------------------------|

**System Parameters**

|                                              |                                     |                   |              |
|----------------------------------------------|-------------------------------------|-------------------|--------------|
| Product family                               | OMNIMATE Signal - series BC/SC 3.81 |                   |              |
| Type of connection                           | Field connection                    |                   |              |
| Wire connection method                       | Clamping yoke connection            |                   |              |
| Pitch in mm (P)                              | 3.81 mm                             |                   |              |
| Pitch in inches (P)                          | 0.15 inch                           |                   |              |
| Conductor outlet direction                   | 180°                                |                   |              |
| Number of poles                              | 20                                  |                   |              |
| L1 in mm                                     | 72.39 mm                            |                   |              |
| L1 in inches                                 | 2.85 inch                           |                   |              |
| Number of rows                               | 1                                   |                   |              |
| Pin series quantity                          | 1                                   |                   |              |
| Rated cross-section                          | 1 mm <sup>2</sup>                   |                   |              |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch              |                   |              |
| Touch-safe protection acc. to DIN VDE 0470   | IP 20                               |                   |              |
| Volume resistance                            | ≤5 mΩ                               |                   |              |
| Can be coded                                 | Yes                                 |                   |              |
| Stripping length                             | 7 mm                                |                   |              |
| Clamping screw                               | M 2                                 |                   |              |
| Screwdriver blade                            | 0.4 x 2.5                           |                   |              |
| Screwdriver blade standard                   | DIN 5264                            |                   |              |
| Plugging cycles                              | 25                                  |                   |              |
| Plugging force/pole, max.                    | 7 N                                 |                   |              |
| Pulling force/pole, max.                     | 5 N                                 |                   |              |
| Tightening torque                            | Torque type                         | Wire connection   |              |
|                                              | Usage information                   | Tightening torque | min. 0.2 Nm  |
|                                              |                                     |                   | max. 0.25 Nm |

**Material data**

|                                       |                               |                                       |        |
|---------------------------------------|-------------------------------|---------------------------------------|--------|
| Insulating material                   | PA 66 GF 30                   | Colour                                | black  |
| Colour chart (similar)                | RAL 9011                      | Insulating material group             | II     |
| Comparative Tracking Index (CTI)      | ≥ 550                         | UL 94 flammability rating             | V-0    |
| Contact material                      | Copper alloy                  | Contact surface                       | tinned |
| Layer structure of plug contact       | 0.5...1.5 µm Cu / 2...5 µm Sn | Storage temperature, min.             | -40 °C |
| Storage temperature, max.             | 70 °C                         | Operating temperature, min.           | -50 °C |
| Operating temperature, max.           | 120 °C                        | Temperature range, installation, min. | -25 °C |
| Temperature range, installation, max. | 120 °C                        |                                       |        |

## BCZ 3.81/20/180 SN BK BX

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Conductors suitable for connection

|                                                                     |                                        |                              |                         |
|---------------------------------------------------------------------|----------------------------------------|------------------------------|-------------------------|
| Clamping range, min.                                                | 0.08 mm <sup>2</sup>                   |                              |                         |
| Clamping range, max.                                                | 1.5 mm <sup>2</sup>                    |                              |                         |
| Wire connection cross section AWG, min.                             | AWG 28                                 |                              |                         |
| Wire connection cross section AWG, max.                             | AWG 16                                 |                              |                         |
| Solid, min. H05(07) V-U                                             | 0.2 mm <sup>2</sup>                    |                              |                         |
| Solid, max. H05(07) V-U                                             | 1.5 mm <sup>2</sup>                    |                              |                         |
| Flexible, min. H05(07) V-K                                          | 0.2 mm <sup>2</sup>                    |                              |                         |
| Flexible, max. H05(07) V-K                                          | 1.5 mm <sup>2</sup>                    |                              |                         |
| w. plastic collar ferrule, DIN 46228 pt 4, 0.2 mm <sup>2</sup> min. |                                        |                              |                         |
| w. plastic collar ferrule, DIN 46228 pt 4, 1.5 mm <sup>2</sup> max. |                                        |                              |                         |
| w. wire end ferrule, DIN 46228 pt 1, min.                           | 0.2 mm <sup>2</sup>                    |                              |                         |
| w. wire end ferrule, DIN 46228 pt 1, max.                           | 1.5 mm <sup>2</sup>                    |                              |                         |
| Plug gauge in accordance with EN 60999 a x b; ø                     | 2.4 mm x 1.5 mm                        |                              |                         |
| Clampable conductor                                                 | Cross-section for conductor connection | Type                         | fine-wired              |
|                                                                     |                                        | nominal                      | 0.5 mm <sup>2</sup>     |
|                                                                     |                                        | Stripping length             | nominal 6 mm            |
|                                                                     | wire end ferrule                       | Recommended wire-end ferrule | <a href="#">H0.5/6</a>  |
|                                                                     |                                        | Type                         | fine-wired              |
|                                                                     |                                        | nominal                      | 0.75 mm <sup>2</sup>    |
|                                                                     |                                        | Stripping length             | nominal 6 mm            |
|                                                                     |                                        | Recommended wire-end ferrule | <a href="#">H0.75/6</a> |
|                                                                     | Cross-section for conductor connection | Type                         | fine-wired              |
|                                                                     |                                        | nominal                      | 1 mm <sup>2</sup>       |
|                                                                     |                                        | Stripping length             | nominal 6 mm            |
|                                                                     |                                        | Recommended wire-end ferrule | <a href="#">H1.0/6</a>  |
|                                                                     | Cross-section for conductor connection | Type                         | fine-wired              |
|                                                                     |                                        | nominal                      | 1.5 mm <sup>2</sup>     |
|                                                                     |                                        | Stripping length             | nominal 7 mm            |
|                                                                     |                                        | Recommended wire-end ferrule | <a href="#">H1.5/7</a>  |

Reference text The outside diameter of the plastic collar should not be larger than the pitch (P). Length of ferrules is to be chosen depending on the product and the rated voltage.

## Rated data acc. to IEC

|                                                                           |                        |                                                                       |                  |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 17.5 A           |
| Rated current, max. number of poles (Tu=20°C)                             | 17.5 A                 | Rated current, min. number of poles (Tu=40°C)                         | 17 A             |
| Rated current, max. number of poles (Tu=40°C)                             | 15.2 A                 | Rated voltage for surge voltage class / pollution degree II/2         | 320 V            |
| Rated voltage for surge voltage class / pollution degree III/2            | 160 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 160 V            |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 2.5 kV                 | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 2.5 kV           |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 2.5 kV                 | Short-time withstand current resistance                               | 3 x 1s with 76 A |

**BCZ 3.81/20/180 SN BK BX****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

**Technical data****Rated data acc. to CSA**

Institute (CSA)



Certificate No. (CSA)

www.weidmueller.com

200039-1121690

Rated voltage (Use group B / CSA) 300 V

Rated voltage (Use group C / CSA) 50 V

Rated current (Use group B / CSA) 8 A

Rated current (Use group C / CSA) 8 A

Wire cross-section, AWG, min. AWG 28

Wire cross-section, AWG, max. AWG 16

Reference to approval values  
Specifications are maximum values, details - see approval certificate.**Packing**

Packaging Box

VPE length 177 mm

VPE width 82 mm

VPE height 64 mm

**Type tests**

Test: Durability of markings

Standard

DIN EN 61984 section 7.3.2 / 09.02 taking pattern from DIN EN 60068-2-70 / 07.96

Test

mark of origin, type identification, rated voltage, rated cross-section, pitch, type of material, approval marking UL, approval marking CSA

Evaluation

available

Test

durability

Evaluation

passed

Test: Misengagement (Non-interchangeability)

Standard

DIN EN 61984 section 6.3 and 6.9.1 / 09.02, DIN EN 60512-13-5 / 11.06

Test

180° turned without coding elements

Evaluation

passed

Test

visual examination

Evaluation

passed

**BCZ 3.81/20/180 SN BK BX****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 2.4.5 / 12.02  
info@weidmueller.com**Technical data**

|                                                           |                |                                                                                                        |                               |
|-----------------------------------------------------------|----------------|--------------------------------------------------------------------------------------------------------|-------------------------------|
| Test: Clampable cross section                             | Standard       | DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 2.4.5 / 12.02<br>info@weidmueller.com |                               |
|                                                           | Conductor type | Type of conductor and conductor cross-section                                                          | solid 0.08 mm <sup>2</sup>    |
|                                                           |                | Type of conductor and conductor cross-section                                                          | stranded 0.08 mm <sup>2</sup> |
|                                                           |                | Type of conductor and conductor cross-section                                                          | solid 1.5 mm <sup>2</sup>     |
|                                                           |                | Type of conductor and conductor cross-section                                                          | stranded 1.5 mm <sup>2</sup>  |
|                                                           |                | Type of conductor and conductor cross-section                                                          | AWG 28/1                      |
|                                                           |                | Type of conductor and conductor cross-section                                                          | AWG 28/19                     |
|                                                           |                | Type of conductor and conductor cross-section                                                          | AWG 16/1                      |
|                                                           |                | Type of conductor and conductor cross-section                                                          | AWG 16/19                     |
|                                                           | Evaluation     | passed                                                                                                 |                               |
| Test for damage to and accidental loosening of conductors | Standard       | DIN EN 60999-1 section 9.4 / 12.00                                                                     |                               |
|                                                           | Requirement    | 0.2 kg                                                                                                 |                               |
|                                                           | Conductor type | Type of conductor and conductor cross-section                                                          | stranded 0.25 mm <sup>2</sup> |
|                                                           |                | Type of conductor and conductor cross-section                                                          | AWG 28/1                      |
|                                                           |                | Type of conductor and conductor cross-section                                                          | AWG 28/19                     |
|                                                           | Evaluation     | passed                                                                                                 |                               |
|                                                           | Requirement    | 0.3 kg                                                                                                 |                               |
|                                                           | Conductor type | Type of conductor and conductor cross-section                                                          | solid 0.5 mm <sup>2</sup>     |
|                                                           |                |                                                                                                        |                               |
|                                                           | Evaluation     | passed                                                                                                 |                               |
|                                                           | Requirement    | 0.4 kg                                                                                                 |                               |
|                                                           | Conductor type | Type of conductor and conductor cross-section                                                          | solid 1.5 mm <sup>2</sup>     |
|                                                           |                | Type of conductor and conductor cross-section                                                          | stranded 1.5 mm <sup>2</sup>  |
|                                                           |                | Type of conductor and conductor cross-section                                                          | AWG 16/1                      |
|                                                           |                | Type of conductor and conductor cross-section                                                          | AWG 16/19                     |
|                                                           | Evaluation     | passed                                                                                                 |                               |

## BCZ 3.81/20/180 SN BK BX

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

## Technical data

|               |                |                                               |                               |
|---------------|----------------|-----------------------------------------------|-------------------------------|
| Pull-out test | Standard       | DIN EN 60999-1 section 9.5 / 12.00            |                               |
|               | Requirement    | ≥10 N info@weidmueller.com                    |                               |
|               | Conductor type | Type of conductor and conductor cross-section | stranded 0.25 mm <sup>2</sup> |
|               |                | Type of conductor and conductor cross-section | AWG 28/1                      |
|               |                | Type of conductor and conductor cross-section | AWG 28/19                     |
|               | Evaluation     | passed                                        |                               |
|               | Requirement    | ≥20 N                                         |                               |
|               | Conductor type | Type of conductor and conductor cross-section | H05V-U0.5                     |
|               |                | passed                                        |                               |
|               |                | ≥40 N                                         |                               |
|               | Conductor type | Type of conductor and conductor cross-section | H07V-U1.5                     |
|               |                | Type of conductor and conductor cross-section | H07V-K1.5                     |
|               |                | Type of conductor and conductor cross-section | AWG 16/1                      |
|               |                | Type of conductor and conductor cross-section | AWG 16/19                     |
|               | Evaluation     | passed                                        |                               |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002638    | ETIM 7.0    | EC002638    |
| ETIM 8.0    | EC002638    | ECLASS 9.0  | 27-44-03-09 |
| ECLASS 9.1  | 27-44-03-09 | ECLASS 10.0 | 27-44-03-09 |
| ECLASS 11.0 | 27-46-02-02 | ECLASS 12.0 | 27-46-02-02 |

## Important note

|                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|----------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.                                                                                                                                                                                                                                                                                                                      |
| Notes          | <ul style="list-style-type: none"> <li>• Additional variants on request</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• Wire end ferrule without plastic collar to DIN 46228/1</li> <li>• Wire end ferrule with plastic collar to DIN 46228/4</li> <li>• P on drawing = pitch</li> <li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>• Long term storage of the product with average temperature of 50 °C and average humidity 70%, 36 months</li> </ul> |

**BCZ 3.81/20/180 SN BK BX****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate No. (cURus) | E60693     |

**Downloads**

|                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|---------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">CB Certificate</a><br><a href="#">CB Testreport</a><br><a href="#">Declaration of the Manufacturer</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Engineering Data                            | <a href="#">EPLAN, WSCAD</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Brochures                                   | <a href="#">FL DRIVES EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL DRIVES DE</a><br><a href="#">FL BUILDING SAFETY EN</a><br><a href="#">FL APPL LED LIGHTING EN</a><br><a href="#">FL INDUSTR.CONTROLS EN</a><br><a href="#">FL MACHINE SAFETY EN</a><br><a href="#">FL HEATING ELECTR EN</a><br><a href="#">FL APPL INVERTER EN</a><br><a href="#">FL BASE STATION EN</a><br><a href="#">FL ELEVATOR EN</a><br><a href="#">FL POWER SUPPLY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a><br><a href="#">PO OMNIMATE EN</a> |

## BCZ 3.81/20/180 SN BK BX

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0


Fax. +49 5231 14-2083

## Drawings


**Dimensional drawing** [info@weidmueller.com](mailto:info@weidmueller.com)




## Graph



## Graph




## Graph




10



BCZ 3.81/.../180 ...



BCZ 3.81/.../180LR ...



BCZ 3.81/.../180F ...



KUNDENZEICHNUNG  
CUSTOMER DRAWING

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

GENERAL TOLERANCE:  
DIN ISO 2768-m



Max. nos.

98178/5  
16.10.17 MA\_J 01  
Modification

**Weidmüller**

Cat.no.: .

**C 40383**

Drawing no. Issue no.  
Sheet 01 of 06 sheets

10



Date Name

Drawn 21.02.2006 GU\_D

Responsible MA\_J

Checked 16.10.2017 ZHOU\_N

Approved XU\_S

Scale: 2/1

Supersedes: .

**BCZ 3.81/.../180 SN ...**  
BUCHSENLEISTE  
SOCKET BLOCK

Product file: BCZ 3.81

7070

|    |         |           |
|----|---------|-----------|
| 20 | 72.39   | 2.850     |
| 19 | 68.58   | 2.700     |
| 18 | 64.77   | 2.550     |
| 17 | 60.96   | 2.400     |
| 16 | 57.15   | 2.250     |
| 15 | 53.34   | 2.100     |
| 14 | 49.53   | 1.950     |
| 13 | 45.72   | 1.800     |
| 12 | 41.91   | 1.650     |
| 11 | 38.10   | 1.500     |
| 10 | 34.29   | 1.350     |
| 9  | 30.48   | 1.200     |
| 8  | 26.67   | 1.050     |
| 7  | 22.86   | 0.900     |
| 6  | 19.05   | 0.750     |
| 5  | 15.24   | 0.600     |
| 4  | 11.43   | 0.450     |
| 3  | 7.62    | 0.300     |
| 2  | 3.81    | 0.150     |
| N  | L1 [mm] | L1 [inch] |