




Dimension

N = Number of poles Δ_3



SIGN	DATE	DESCRIPTION	APPROVER
△	01/26/07	Soldering temperature changed from 245° to 250°	Tason
△	01/26/07	Part NO is Changed	Tason
△	9/01/08	增加公差標注	Seamus
△	9/01/08	Operating temperature changed from -30°C/+105°C to -40°C/+115°C	Seamus
△	12/08/10	Add is " TUV "	Aaron

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item 1 Terminal housing :Thermoplastic (UL 94V-0)
- Item 2 Clamp : Brass,Ni plated
- Item 3 Wire guard solder pin : Brass,Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-"/slot type

Electrical cULus / TUV

- Voltage rating: 300V / 300V
- Current rating: 10A / 12A
- Wire range: 0.2~1.5mm²
- Solid wire(AWG): 16-24
- Stranded wire(AWG): 16-24
- Torque: 1.7 Lb.in / 0.2Nm (stackable type: 1.5Kgf cm)
- Screw: M2
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV / 1.25KV
- △ Operating temperature: -40°C to +115°C
- △ Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:  

CRAUS TÜRK

2 YO xx 21 x 0 xxxx G

RoHS
Pb < 40,000 ppm

No. of poles	0	Black (RAL9005)	0000 Standard @ Logo
02 2 CONTACTS	5	Green(RAL6018/T)	000A Standard ANY Logo
03 3 CONTACTS	6	Blue (RAL5015/A)	Any special item by
... ..	8	Grey(RAL7035/D)	customer request,
24 24 CONTACTS	C	Green(RAL6018/U)	please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YO 3.81 Series 2p-24p				
PART NO.		Y0xx21x0xxxxG		DWG NO.	8Y00101	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance	
			Chen Bo 2011.04.02		UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30
				SHEET: 01/01	REV: G	X.XX ±0.10
					X° ±1°	