

D

C

B




A

D

C




B

A



RECOMMENDED PANEL CUTOUT

DETAIL A



DETAIL B

- CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
- WILL ACCEPT THIRTY-SEVEN (37) MULTIMATE PIN CONTACTS.
- NO 4 FASTENER RECOMMENDED FOR MOUNTING.
- WHITE DOT NEAR POSTION 1 ON WIRE ENTRY FACE.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- MATERIALS:
HOUSINGS: PA66, BLACK
PERIPHERAL SEAL: NITRILE BUTADIENE RUBBER
THREADED INSERT: BRASS
- TE LOGO AND PART NUMBER LOCATED ON ANY FLANGE EDGE

4	#4-40 THREADED INSERT	STANDARD	NO	A	206151-9
	Ø.150 MOUNTING HOLES	STANDARD	YES	A	206151-8
5	Ø.150 MOUNTING HOLES	STANDARD	NO	A	206151-6
	Ø.150 MOUNTING HOLES	SMALL PACK	NO	A	206151-5
6	NONE	STANDARD	YES	B	206151-4
	Ø.150 MOUNTING HOLES	STANDARD	YES	A	206151-3
7	NONE	STANDARD	NO	B	206151-2
	Ø.150 MOUNTING HOLES	STANDARD	NO	A	206151-1
MOUNTING FEATURE		PACKAGING	PERIPHERAL SEAL	SEE DETAIL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SCHLEGEL 06DEC2002	TE Connectivity		
DIMENSIONS: INCHES		CHK A. FRANTUM 8/13/83			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. STONE 8/13/83	NAME		
0 PLC ± .005		PRODUCT SPEC	RECEPTACLE HOUSING, STANDARD SEX, SHELL SIZE 23, CPC		
1 PLC ± .005		APPLICATION SPEC			
2 PLC ± .005		WEIGHT	SIZE CAGE CODE DRAWING NO		
3 PLC ± .005		REVISION	A1 00779 206151		
4 PLC ± .005		DATE	CUSTOMER DRAWING		
ANGLES		SCALE	2:1		
FINISH		SHEET	1 OF 1		
REV		REV	R		