






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

SUGGESTED PCB LAYOUT




UNIT:mm / INCH
TOLERANCES: ± 0.10 / 0.004
ONLY FOR THIS VIEW

CONNECTOR BOUNDRY



METAL PANEL



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SHARMA 27AUG2016	TE Connectivity Ltd.		
		CHK O. WIBORG 27AUG2016			
		APVD J. DE BRUIJN 27AUG2016	NAME RJ45 JACK INT.MAG. 10/100 LED 1x2 INV.		
DIMENSIONS: mm [INCHES]		PRODUCT SPEC 108-94552			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-94447			
MATERIAL		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-2301996-5
			RESTRICTED TO —		
			SCALE 3:1	SHEET 2 OF 3	REV B1

