





1-2013928-6 Product Details



1-2013928-6

TE Internal Number: 1-2013928-6



Active

FPC (Flexible Printed Circuit) Connectors

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- .30 mm Centerline
- 41 Positions
- Gold Contact Plating, Mating Area, Material
- Contact Plating, Mating Area, Thickness = .1 μ m
- Thermoplastic Housing Material

[View all Features](#)

Quick Links

- [Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

Additional Information:

- [Product Information](#)
- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- PCB Mounting Orientation = Right Angle
- PCB Mount Alignment = Without
- PCB Mount Retention = Without
- Actuator Type = Rear Flip (Front Hinge)
- PCB Mount Retention Type = Solder Pads
- Sealed = No

Electrical Characteristics:

- Contact Current Rating, Max. (A) = 0.2
- Operating Voltage Reference = AC
- Operating Voltage (VAC) = 50

Termination Features:

- Termination Method to PC Board = Surface Mount

Dimensions:

- Flex Cable Thickness (mm [in]) = 0.2 [0.008]
- Length (X-Axis) (mm [in]) = 12.80 [0.5039]
- Width (Z-Axis) (mm [in]) = 3.80 [0.1496]
- Profile Height (Y-Axis) (mm [in]) = 0.90 [0.035]

Body Features:

- Selectively Loaded = No

Contact Features:

- Contact Plating, Mating Area, Material = Gold
- Contact Plating, Mating Area, Thickness (μ m [μ in]) = 0.1 [3.937]
- Contact Plating, Termination Area, Material = Gold
- Contact Plating, Termination Area, Thickness (μ m [μ in]) = 0.1 [3.93]
- Contact Design = Single Beam
- Contact Base Material = Copper Alloy

Housing Features:

- Centerline (mm [in]) = 0.30 [0.012]
- Housing Material = Thermoplastic
- Contact Mating Location = Bottom
- Housing Color = Natural

Configuration Features:

- Number of Positions = 41
- Tail Orientation = Staggered
- Shrouded = Yes
- Shielded = No
- Strain Relief = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Identification Marking:

- Circuit Identification Feature = Without

Environmental:

- Operating Temperature ($^{\circ}$ C [$^{\circ}$ F]) = -25 - +85 [-13 - +185]

Operation/Application:

- ZIF/Non-ZIF = ZIF
- Contact Transmits (Typical Application) = Signal (Data)
- Pick and Place Cover = Without

Packaging Features:

- Packaging Method = Tape & Reel

Other:

- Brand = TE Connectivity

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

[Privacy Policy](#)

[AODA Accessibility Policy](#)

[AODA Multi-Year Accessibility
Plan](#)

[Product Compliance Support Center](#)

[Site Map](#)

[Manage Your Account](#)

