




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	6	IMPROVE THE HOUSING PIN HOLES	30MAY2019	T.Z	B.L




1. MATERIAL
1 HOUSING : HIGH TEMP, THERMO-PLASTIC, UL94V-0, BLACK
2 CONTACT : COPPER ALLOY
2. FINISH
CONTACT : 3u"Au PL. ON CONTACT AREA
Ni UNDER PL. 50u" MIN.OVER ALL.
3. THICKNESS:1.219mm AFTER COMPRESSION.
4. DIMENSION SHALL BE INTERPRETED PER ASME Y14.5M-1994.
5. RECOMMENED CONNECTOR LOADING FORCE:10Kgf Min.



CONTACT CROSS SECTION DETAIL



DETAIL A
SCALE 10:1




THIS PRINT IS
PRELIMINARY
UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

2350616-1	1
PART NO.	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. Z 10JAN2019 CHK S. L 10JAN2019 APVD S. L 10JAN2019		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.10 3 PLC ±0.05 4 PLC ±- ANGLES ±1 FINISH -		NAME CUSTOMER DRAWING DMD SOCKET LGA250	
MATERIAL -		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE A2 CAGE CODE 00779 DRAWING NO C-2350616 RESTRICTED TO	
CUSTOMER DRAWING				SCALE 2:1	SHEET 1 of 2
				REV A1	

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.Z	10JAN2019	TE Connectivity	
DIMENSIONS:		CHK S.L	10JAN2019		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S.L	10JAN2019	NAME CUSTOMER DRAWING DMD SOCKET LGA250	
MATERIAL		PRODUCT SPEC		SIZE	
		APPLICATION SPEC		CAGE CODE	
		WEIGHT		DRAWING NO	
		CUSTOMER DRAWING		RESTRICTED TO	
				SCALE 2:1	
				SHEET 2 OF 2	
				REV A1	