




Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Cable Clamp Kit**
Primary Product Material: **ABS**
Compatible With Connector Shell Size: **4**
Shielded: **Yes**
Number of Positions: **37**

Features

Product Type Features

Strain Relief Accessory Type	Cable Clamp Kit
------------------------------	-----------------

Configuration Features

Number of Positions	37
---------------------	----

Body Features

Cable Exit Angle	180°
Primary Product Material	ABS

Mechanical Attachment

Thread Size	M2.6
-------------	------

Housing Features

Compatible With Connector Shape	D-Shaped
Body Orientation	Straight

Dimensions

Compatible Insulation Diameter Range	12.7 mm[.5 in]
--------------------------------------	----------------

Operation/Application



Compatible With Connector Shell Size	4
Shielded	Yes

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5748678-4
2 PC PLST CBL CLMP KIT

TE Part # 1747253-1
UNC 4-40 SCREW KIT 1000 EACH A

TE Part # 1-172996-3
M2.6 CROSS-RECESSED HEAD SCREW

TE Part # 174194-1
WASHER

TE Part # 174456-1
MOUNTING SCREW (M2.6)

Also in the Series | **AMPLIMITE Kit**

Connector Caps & Covers(3)

Connector Hardware(104)

Connector Seals & Cavity Plugs(4)

Connector Strain Relief(144)

Customers Also Bought

TE Part #1658612-1
37 POS HDF RCPT, MS, LEAD FREE

TE Part #1-1827862-5
DYNAMIC 1100D REC HSG 10P X BLACK

TE Part #1-1903130-6
DYNAMIC 1200D TAB HSG 12P F/H

TE Part #1827570-2
DYNAMIC D1000 REC CONT M AU 0.38um FORM

TE Part #747275-1
037 LP HDF STRAIN RELIEF

TE Part #1-172161-9
MINI UNIVERSAL M-N-L CAP 9P

TE Part #170359-1
UNIV M-N-L PIN 26-22 AWG

TE Part #917572-4
1.5 B-T-W PLUG HSG 4P BLACK



Documents

Product Drawings

AMPLIMITE CABLE CLAMP 37P KIT

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-172928-3_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-172928-3_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-172928-3_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Terminating AMP MTEI Connector

English

Application Specification

English