




REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
	B1	REVISED PER ECO-15-001494	05FEB2015	AP	DD



⚠ MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.

⚠ FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.



192X $\varnothing 0.39 \pm 0.05$
 $\varnothing 0.10$
PLATED THRU HOLE

UNGUIDED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 13JAN2011	 TE Connectivity					
		CHK J. EABY 13JAN2011						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.25 1 PLC ±0.25 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH -	NAME					
			IMPACT, 4 PAIR, 16 COLUMN, HEADER UNGUIDED, DUAL END WALL SIGNAL MODULE, 0.39 PTH					
MATERIAL		SEE TABLE	PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
			APPLICATION SPEC					
					WEIGHT	A1	00779C=	2007838
CUSTOMER DRAWING			SCALE	6:1	SHEET	1	OF 2	REV B

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

	5.5	2007838-3
	4.9	2007838-2
	4.5	2007838-1
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER	13JAN2011	 TE Connectivity			
DIMENSIONS:		CHK J. EABY	13JAN2011				
mm		APVD J. EABY	13JAN2011	NAME	IMPACT, 4 PAIR, 16 COLUMN, HEADER UNGUIDED, DUAL END WALL SIGNAL MODULE, 0.39 PTH		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO				
0 PLC ±		APPLICATION SPEC		A 00779 C=2007838 -			
1 PLC ±0.25		WEIGHT -				CUSTOMER DRAWING	
2 PLC ±0.13							
3 PLC ±							
4 PLC ±		ANGLES ±		SCALE 5:1 SHEET 2 OF 2 REV B1			
FINISH		SEE TABLE					
MATERIAL							
-							
-							