





PANEL CUTOUT

PANEL THICKNESS	(x)	TOLERANCE
0.75 - 1.25 mm	30.0	+0.1/-0
1.25 - 2.00 mm	30.2	+0.1/-0
2.00 - 3.00 mm	30.5	+0.1/-0



NOTE:

- DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACT MATERIAL: SILVER
- CONTACT RATINGS:
ANSI/UL 1054:
16A @ 125/250VAC [cURus]
20A @ 250VAC [cURus]
3/4HP 125/250VAC [cURus]
- CONTACT RESISTANCE: 20mΩ MAX. INITIAL
- INSULATION RESISTANCE: 100MΩ MIN. @ 500VDC
- DIELECTRIC STRENGTH: 1,000VAC FOR 1 MINUTE
- ELECTRICAL LIFE: 6,000 CYCLES [cURus]
- OPERATING TEMPERATURE: 0°C to 65°C [cURus]
- ▲ DENOTES CRITICAL PARAMETER
- ILLUMINATION: N/A



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-100562	REMOVE VDE/ENEC/CSA, UPDATE RATINGS	12/30/21	JS	TITLE RB141D2211				000000285
					SCALE 1:1	DATE 6/17/2020	DR MW	DWG 14-RB141D2211	REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED