




- NOTES: UNLESS OTHERWISE SPECIFIED
 1. FOR GENERAL SERIES SPECIFICATIONS, SEE SD361-0000
 2. DESIGNED FOR USE WITH RG-316 OR EQUIVALENT CABLE
 3. MATERIAL SPECIFICATIONS:
 INSULATOR: PTFE
 BODY AND CONTACT: BERYLLIUM COPPER
 FERRULE: COPPER
 ALL OTHER METAL PARTS: BRASS
 4. FINISH SPECIFICATIONS:
 CONTACT: .000003 MIN THICK GOLD OVER .000050 MIN THICK NICKEL
 ALL OTHER METAL PARTS: .000003 MIN THICK GOLD OVER .000080 MIN THICK NICKEL
 5. ELECTRICAL SPECIFICATIONS:
 IMPEDANCE: 50 OHMS
 FREQUENCY RANGE: DC-3.0GHz
 6. CAP AND FERRULE SHIPPED LOOSE
 7. CRIMP WITH .128" HEX DIE.

REV	DESCRIPTION	BY	DATE	APPD
A	ER057281	CV	04/22/15	J



RECOMMENDED TRIM DIMENSION

CATALOG P/N: 2021B504-316

PER ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [MM] TOLERANCES: DECIMAL: .XX [XX] ± .01 [0.3] .XXX [XXX] ± .005 [0.13] .XXXX [XXXX] ± .0005 ANGLES: ± 2° SCALE: 6:1				 Winchester Electronics Corporation 199 Park Road Ext Suite 104 Middletown, Connecticut 06762			
CUSTOMER SALES DRAWING				SMP, R/A PLUG FOR RG-316 OR EQUIVALENT CABLE (ROHS)			
DRAWN	DATE	APPROVED	DATE	DRAWN	DATE	APPROVED	DATE
CV	04/14/15	J	04/22/15	CV	04/14/15	J	04/22/15
XXX	XX/XX/XX	XXX	XX/XX/XX	XXX	XX/XX/XX	XXX	XX/XX/XX
A				SD2021B504-316			
				1 1			
				A			