




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
-	-	A		INITIAL RELEASED	2016-2-3	AY

NOTES:

1. PRODUCT SPECIFICATION:
CURRENT RATING: 2.0AMP
CONTACT RESISTANCE: 20mΩ MAX
WITHSTAND VOLTAGE: 1000V AC/DC
INSULATION RESISTANCE: 10E6MΩ MIN
OPERATING TEMPERATURE: -55℃ to +105℃
RECOMMEND SOLDERING PROCESS: WAVE SOLDERING
PEAK TEMPEREATURE:250℃

- 2 MATERIAL
CONTACT: COPPER ALLOY
HOUSING: LOW-TEMPRATURE MATERIAL UL94V-0
- 3 1.27um MIN NICKEL PER TEC-112-25 UNDERPLATE ALL OVER
4 2.54um MIN TIN PER TEC-112-65 ON SOLDERING AREA
5 0.76um MIN GOLD PER TEC-112-162 ON CONTACT AREA
6 0.25um MIN GOLD PER TEC-112-162 ON CONTACT AREA
7 0.076um MIN GOLD FLASH PER TEC-112-33 ON CONTACT AREA
8. PARTS MUST CONFORM TO DIN41612/IEC60603-2
9. PART NO X-2271290-1,-2 IS NOT RELEASED



4.57	3 4 5	abc	48	8-2271290-2
4.57	3 4 6	abc	48	8-2271290-1
4.57	3 4 7	abc	48	8-2271290-0
4.57	3 4 5	a c	32	7-2271290-2
4.57	3 4 6	a c	32	7-2271290-1
4.57	3 4 7	a c	32	7-2271290-0
4.0	3 4 5	abc	48	6-2271290-2
4.0	3 4 6	abc	48	6-2271290-1
4.0	3 4 7	abc	48	6-2271290-0
4.0	3 4 5	a c	32	5-2271290-2
4.0	3 4 6	a c	32	5-2271290-1
4.0	3 4 7	a c	32	5-2271290-0
3.0	3 4 5	abc	48	4-2271290-2
3.0	3 4 6	abc	48	4-2271290-1
3.0	3 4 7	abc	48	4-2271290-0
3.0	3 4 5	a c	32	3-2271290-2
3.0	3 4 6	a c	32	3-2271290-1
3.0	3 4 7	a c	32	3-2271290-0
2.5	3 4 5	abc	48	2-2271290-2
2.5	3 4 6	abc	48	2-2271290-1
2.5	3 4 7	abc	48	2-2271290-0
2.5	3 4 5	a c	32	1-2271290-2
2.5	3 4 6	a c	32	1-2271290-1
2.5	3 4 7	a c	32	1-2271290-0
DIM.A	FINISH	ROWS LOADED	POS	PN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ANDY YANG	27JAN2016	TE Connectivity	
DIMENSIONS: mm		CHK RICK BIAN	APVD XIAN XU		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	108-137009	NAME	
MATERIAL		APPLICATION SPEC	-	DIN CONNECTOR, TYPE 2C, 48 PIN	
SEE NOTE		WEIGHT	-	HEADER, RIGHT ANGLE	
SEE NOTE		CUSTOMER DRAWING	-	WITH CLIPS	
SCALE 1:1		SHEET 1 OF 1		REV A	