

Subminiature Fuse, 4.05 x 10 mm, Quick-Acting F, 250 VAC, 125 VDC



UL 248-14 · 250 VAC · 125 VDC · Quick-Acting F

See below:

[Approvals and Compliances](#)

## Description

- Low Breaking Capacity

## References


Last order date: 30.04.2021

We recommend for new applications [SPT 3.6x10](#)

## Weblinks

[pdf data sheet](#), [html datasheet](#), [General Product Information](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

## Technical Data

Rated Voltage	125 - 250 VAC, 125 VDC
Rated current	0.05 - 5 A
Breaking Capacity	50 A - 300 A
Characteristic	Quick-Acting F
Admissible Ambient Air Temp.	-40 °C to 85 °C
Material: Tube	Ceramics
Material: Axial Leads	Tin-Plated Copper
Unit Weight	0.6 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	 , Rated current, Characteristic

Soldering Methods	Wave <a href="#">Soldering Profile</a>
Solderability	235 °C / 2 sec acc. to IEC 60068-2-20, Test Ta, method 1
Resistance to Soldering Heat	260 °C / 5 sec acc. to IEC 60068-2-20, Test Tb, method 1A

## Approvals and Compliances


Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [Details about Approvals](#)

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

## Approvals



The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products.

Approval Reference Type: 172593

Approval Logo	Certificates	Certification Body	Description
	<a href="#">UL Approvals</a>	UL	UL File Number: E42088


## Product standards

Product standards that are referenced

Organization	Design	Standard	Description
	Designed according to	UL 248-14	Low voltage fuses - Part 14: Additional fuses
	Designed according to	CSA22.2 No. 248.14	Low-Voltage Fuses - Part 14: Supplemental Fuses






Application standards

Application standards where the product can be used


Organization	Design	Standard	Description
	Designed for applications acc.	IEC/UL 62368-1	Audio/video, information and communication technology equipment - Part 1: Safety requirements

Compliances

The product complies with following Guide Lines

Identification	Details	Initiator	Description
	<a href="#">CE declaration of conformity</a>	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
	<a href="#">UKCA declaration of conformity</a>	SCHURTER AG	The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.
	<a href="#">RoHS</a>	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
	<a href="#">China RoHS</a>	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
	<a href="#">REACH</a>	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.


Dimension [mm]




Pre-Arcing Time


Rated Current In	1.0 x In min.	2.0 x In max.	3.0 x In max.
0.05 A - 5 A	4 h	60 s	100 ms

## Time-Current-Curves



## All Variants

Rated Current [A]	Rated Voltage [VAC]	Rated Voltage [VDC]	Breaking Capacity	Voltage Drop 1.0 I <sub>n</sub> typ. [mV]	Melting I <sup>2</sup> t 10.0 I <sub>n</sub> typ. [A <sup>2</sup> s]		Order Number
0.05	250	125	1)	1150	0.00011	●	7010.1740.46
0.063	250	125	1)	735	0.00035	●	7010.1750.46
0.08	250	125	1)	950	0.00039	●	7010.1760.12
0.1	250	125	1)	875	0.00079	●	7010.1770.12
0.1	250	125	1)	875	0.00079	●	7010.1770.46
0.125	250	125	1)	870	0.0013	●	7010.1780.12
0.125	250	125	1)	870	0.0013	●	7010.1780.46
0.15	250	125	1)	545	0.0029	●	7010.1790.12
0.15	250	125	1)	545	0.0029	●	7010.1790.46
0.2	250	125	1)	520	0.0071	●	7010.1910.12
0.2	250	125	1)	520	0.0071	●	7010.1910.46
0.3	250	125	1)	920	0.021	●	7010.1920.12
0.3	250	125	1)	920	0.021	●	7010.1920.46
0.4	250	125	1)	725	0.057	●	7010.1930.12
0.4	250	125	1)	725	0.057	●	7010.1930.46
0.5	250	125	1)	725	0.069	●	7010.1800.46
0.6	250	125	1)	205	0.059	●	7010.1810.12
0.6	250	125	1)	205	0.059	●	7010.1810.46
0.8	250	125	1)	150	0.095	●	7010.1820.12
0.8	250	125	1)	150	0.095	●	7010.1820.46
1	250	125	1)	185	0.12	●	7010.1830.46
1.25	250	125	1)	125	0.29	●	7010.1840.12
1.25	250	125	1)	125	0.29	●	7010.1840.46
1.6	250	125	1)	135	0.48	●	7010.1850.12
1.6	250	125	1)	135	0.48	●	7010.1850.46
2	250	125	1)	110	0.95	●	7010.1860.12
2	250	125	1)	110	0.95	●	7010.1860.46
2.5	250	125	1)	145	1.2	●	7010.1870.12

Rated Cur- rent [A]	Rated Vol- tage [VAC]	Rated Vol- tage [VDC]	Breaking Capacity	Voltage Drop 1.0 I <sub>n</sub> typ. [mV]	Melting I <sup>2</sup> t 10.0 I <sub>n</sub> typ. [A <sup>2</sup> s]		Order Number
2.5	250	125	1)	145	1.2	●	7010.1870.46
3	250	125	1)	220	1.8	●	7010.1880.12
3	250	125	1)	220	1.8	●	7010.1880.46
4	250	125	1)	130	3.4	●	7010.1890.12
4	250	125	1)	130	3.4	●	7010.1890.46
5	250	125	1)	105	7.7	●	7010.1900.12
5	250	125	1)	105	7.7	●	7010.1900.46

Availability for all products can be searched real-time:<https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

1) 50 A @ 250 VAC/DC; 300 A @ 125 VAC/DC

Packaging Unit	.xx = .12	Plastic Bag (50 pcs.)
	.xx = .46	Taped 19 cm Reel (1000 pcs.)