




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		B1	REVISED PER ECO-15-001498	02FEB2015	AP	DD

⚠ MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.



⚠ FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.



96X Ø0.46±0.05
PLATED THRU HOLE

96X Ø0.55±0.013
DRILL HOLE
⊕ Ø0.10

UNGUIDED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COELLO 27APR2011	TE Connectivity	
DIMENSIONS:		CHK J. EABY 27APR2011		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. EABY 27APR2011	NAME IMPACT, 2 PAIR, 16 COLUMN, HEADER	
	0 PLC ±	PRODUCT SPEC	UNGUIDED, RIGHT END WALL	
	1 PLC ±0.25	APPLICATION SPEC	SIGNAL MODULE, 0.46 PTH	
	2 PLC ±0.13			
	3 PLC ±		SIZE CAGE CODE DRAWING NO	
	4 PLC ±		A100779C=2057747	
MATERIAL	FINISH SEE TABLE	WEIGHT	RESTRICTED TO	
		Customer Drawing	SCALE 6:1 SHEET 1 OF 2 REV B1	

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-

	5.5	2057747-3
	4.9	2057747-2
	4.5	2057747-1
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COELLO	27APR2011	 TE Connectivity						
DIMENSIONS:	mm	CHK J. EABY	27APR2011	NAME	IMPACT, 2 PAIR, 16 COLUMN, HEADER UNGUIDED, RIGHT END WALL SIGNAL MODULE, 0.46 PTH					
		APVD J. EABY	27APR2011							
	0 PLC ± 1 PLC ±0.25 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ± FINISH	TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC						
		APPLICATION SPEC		SIZE						
		SEE TABLE		CAGE CODE						
MATERIAL	-	WEIGHT		DRAWING NO		RESTRICTED TO				
-		Customer Drawing		A100779		©=2057747				
				SCALE		SHEET				
				5:1		2				
				OF		2				
				REV		B1				