



SQUARE FLANGE JACK RECEPTACLE
WITH CYLINDRICAL CONTACT - PACK. 50

R128.414.701



Series : BMA




PANEL CUT OUT

A DIA
 B DIA
 4 holes

	mm	
	Maxi	mini
A	4.14	4.1
B	2.8	2.6
C	8.66	8.62



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
BODY	STAINLESS 303	PASSIVATED
CENTER CONTACT	BERYLLIUM COPPER	GOLD 1.3 OVER NICKEL 2
OUTER CONTACT	BERYLLIUM COPPER	NPGR
INSULATOR	PTFE	
GASKET		
OTHERS PARTS	BRASS	NPGR
-	-	-
-	-	-

Issue : 1302 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RADIAL 

SQUARE FLANGE JACK RECEPTACLE
WITH CYLINDRICAL CONTACT - PACK. 50

R128.414.701

Series : BMA

PACKAGING

Standard	Unit	Other
50	'W' option	Contact us

SPECIFICATION**ELECTRICAL CHARACTERISTICS**

Impedance	50	Ω
Frequency	0-22	GHz
VSWR	1.25* + 0,0000	x F(GHz) Maxi
Insertion loss	.07	$\sqrt{F}(\text{GHz})$ dB Maxi
RF leakage	- (NA	- F(GHz)) dB Maxi
Voltage rating	500	Veff Maxi
Dielectric withstanding voltage	1500	Veff mini
Insulation resistance	5000	M Ω mini

ENVIRONMENTAL

Operating temperature	-65/+165	$^{\circ}\text{C}$
Hermetic seal	NA	Atm.cm3/s
Panel leakage	NA	

OTHER CHARACTERISTICSAssembly instruction **NA**

Others :

* de 0-10 GHz

MECHANICAL CHARACTERISTICS

Center contact retention	
Axial force – Mating end	27 N mini
Axial force – Opposite end	27 N mini
Torque	NA N.cm mini
Recommended torque	
Mating	NA N.cm
Panel nut	NA N.cm
Mating life	1000 Cycles mini
Weight	3,4800 g

Issue : 1302 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RADIAL 