








SWITCH FUNCTION ▲		
POS. 1	POS. 2	POS. 3
ON	OFF	(ON)
2-3	N/A	2-1

NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERMINAL NUMBERS FOR REF ONLY
- PLATING MATERIAL: GOLD
- RATING: 0.4 VOLT AMPS MAX. @20V MAX. AC OR DC
- ELECTRIC LIFE: 40,000 make-and-break cycles at full load.
- INSULATION RESISTANCE: 1,000 Mega-ohm min.
- DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
- OPERATING TEMP.: -30°C to 85°C
- ▲ DENOTES CRITICAL PARAMETER.
- 2002/95/EC (ROHS) COMPLIANT



BLACK ACTUATOR ▲



E-SWITCH™

B	17851	Corrected Function on Switch Body	11/9/07	rc
A	17831	New Release	11/7/2007	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE 300SP5R8BLKVS2RE

SCALE 2=1

DATE 11/7/2007

DR rc

DWG T311011

REV B