









PCB LAYOUT



▲ CIRCUIT: SPST



NOTES:

1. ALL DIMENSIONS IN MM [INCH]: x.x = ± 0.4
x.xx = ± 0.25
2. TERMINAL NUMBERS FOR REF. ONLY
3. CONTACT MATERIAL: SILVER
4. CONTACT RATING: 50mA; 12 VDC
5. TRAVEL: 0.2 ± 0.1 mm
- ▲ 6. OPERATING FORCE: 400 ± 80 gf
7. ELECTRICAL LIFE: 100,000 CYCLES
8. CONTACT RESISTANCE: $100\text{m}\Omega$ MAX.
9. ▲ DENOTES CRITICAL PARAMETER
10. INSULATION RESISTANCE: $100\text{M}\Omega$ MIN @ 100VDC.
11. DIELECTRIC STRENGTH: 250VAC FOR 1 MINUTE WITH NO BREAK DOWN



A	24310	Release	5/18/20	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE TL3365AF400QG				
SCALE 8:1	DATE 5/18/2020	DR MW	DWG P003111	REV A