




REV. 0

DC0 141065

COIL: @ 25°C

RESISTANCE 125 OHMS ±10%

NOMINAL VOLTAGE 6.0 VDC

MUST OPERATE 3.5 VDC

MUST RELEASE 2.0 VDC MAX., 0.28 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX.

RELEASE TIME 2.0 MS MAX.

CONTACT STABILIZATION TIME 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 5/14/99

CK. 5/14/99



COMMUNICATIONS
INSTRUMENTS, INC.

CUST. QPL

CUST. NO. M39016/7-015M

TYPE "J1MA" RELAY

J1MAW-6XM