




LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E	REVISED PER ECR-12-013486	08JAN13	KH	KR




- 1 MATL: #2 HARD BRASS OR NICKEL PLATED STEEL.
- 2 NO BURRS PERMISSIBLE AT HOLE.
- 3 TIN PLATING IS REQUIRED ON BRASS WHEN
TERMINAL TEMPERATURE IS OVER 225°F
- 4 MUST BE FLAT WITHIN 0.076 [.003] OVER
THIS LENGTH.
- 5 HOLE MUST BE SYMMETRICAL ABOUT TAB $\perp$
WITHIN 0.076 [.003].
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



- 1 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 2 CONTINUOUS STRIP ON REELS.
- 3  THIS DIMENSIONS MUST BE MAINTAINED FOR PROPER FUNCTION OF THE LATCHING MECHANISM.
- 4 WIRE SIZE IS 0.5–1.4mm [20–16] AWG
- 5 INSULATION RANGE IS 1.52–2.79 [.060–.110] DIA



VIEW A—A



SECTION B-B

SECTION C-C

F OR O	3.56 [.140]	4.78 [.188]	F	2.29 [.090]	1.448 [057] 1.27 [050] 1.143 [045]	1.3mm [16] 0.8mm [18] 0.5mm [20]
TYPE	WIDTH	STRIP LENGTH ±.015	TYPE	WIDTH	±.051 [±.002] HEIGHT	WIRE
INSUL BARREL CRIMP			WIRE BARREL CRIMP			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 10/12/89 CHK MS FEHER 10/12/89 APVD R KUZO 10/12/89		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.25 [.010] 4 PLC ± ± - ANGLES		NAME RECEPTACLE, POSITIVE LOCK, 4.75 [.187] SERIES	
		PRODUCT SPEC — APPLICATION SPEC —			
MATERIAL BRASS		FINISH SEE TABLE		SIZE A2	CAGE CODE 00779
		WEIGHT —		DRAWING NO C-63498	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 5:1	SHEET 1 of 1
				REV F	