





CATALOG LISTING
21EN31-R1
PAGE 1 OF 1
ISSUE
19
REPLACES
RELEASE NO.
CHECK
CHECK
CHECK
30 JUN 98
J A F
CHECK
24 JUN 98
J A S
DRAWN
MASTER



- NOTES
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
 - (3) TO ADJUST ROLLER DIRECTION, REMOVE ROLLER GUIDE LOCK RING, SCREW ROLLER GUIDE DOWN AS FAR AS POSSIBLE, THEN UNSCREW TO DESIRED DIRECTION. SECURE BY REPLACING ROLLER GUIDE LOCK RING
 - 4 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
 - 5 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
 - (6) HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH			THIRD ANGLE PROJECTION	
CHARACTERISTICS			SCALE FULL	
OPERATING FORCE ----- 6 - 12 LB			DO NOT SCALE PRINT	
FULL OVERTRAVEL FORCE ----- 30 LB MAX			UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE ----- 4 LB MIN			ONE PLACE (.0) ±.030	
PRETRAVEL ----- .040 MAX			TWO PLACE (.00) ±.015	
DIFFERENTIAL TRAVEL ----- .020 MAX			THREE PLACE (.000) ±.005	
OVERTRAVEL ----- .250 MIN			ANGLES ±	
ELECTRICAL DATA			WEIGHT 6 OZ MAX	
CONTACT ARRANGEMENT			ANSI Y14.5M-1982 APPLIES	
2X S P D T				
LOAD	28 VDC			
	SEA LEVEL	50,000 FT.		
RES	4	4		
IND	2	2		
MOTOR	4			