


Connectors > Terminal Blocks & Strips > Barrier Strips



Barrier Strip Style: **Tri-Barrier**

Bottom Termination Style: **Printed Circuit**

Current Rating: **10 A**

Number of Positions: **11**

Centerline (Pitch): **6.35 mm [ .25 in ]**

## Features

### Product Type Features

Product Type	Barrier Strip
Block Style	Open Bottom with Standoffs
Connector & Contact Terminates To	Printed Circuit Board

### Configuration Features

Number of Levels	1
Number of Positions	11
Number of Rows	1

### Electrical Characteristics

Current Rating (Max)	10 A
Current Rating	10 A
Voltage	300 V

### Body Features

Color	Black
Barrier Strip Style	Tri-Barrier

### Contact Features

Terminal Plating Material	Tin
Terminal Material	Copper Alloy
Terminal Plating Finish	Bright

### Termination Features

## Bottom Termination Style

## Printed Circuit

**Mechanical Attachment**

Mounting Angle

Right Angle

Screw Head Type

Wire Clamp Combo Head

Mounting Insert

Without

Top Hardware

Wire Clamp Combo Head

Screw Plating Material

Zinc

Screw Plating Finish

Bright

Screw Material

Steel

Mounting Options

None

Mounting Ears

Without

Screw Size

M3

**Housing Features**

Housing Material

Thermoplastic

Centerline (Pitch)

6.35 mm[.25 in]

**Dimensions**

Length

71.63 mm[2.8 in]

Wire Size

.05 – 1.4 mm<sup>2</sup>**Industry Standards**

UL Flammability Rating

UL 94V-0

**Packaging Features**

Packaging Method

Package

**Other**

Comment

Other options available upon request,  
consult our Product Information Center.**Product Compliance**For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2019  
(197)

Candidate List Declared Against: JAN 2019  
(197)

Halogen Content

BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.


Solder Process Capability

Wave solder capable to 265°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Also in the Series | Buchanan 3 Series



Barrier Strips(61)

## Customers Also Bought



TE Part #1487597-1  
USB, A-B, 25/22, BLACK,  
3.0M




TE Part #1604210-1  
UMNL BULKHEADCONN,  
6 POS



TE Part #770904-4  
MINI UMNL SOK CONT  
22-18 AWG



TE Part #1604254-1  
UMNL BULKHEADCONN,  
9 POS

TE Part #360041-1  
FASTON 187 TAB HSG  
NYLON NATTE Part #1604941-1  
UMNL BULKHEAD CONN,  
12 POSTE Part #2-1546119-9  
3PCV-11-006=3PCV  
AssemblyTE Part #1546307-8  
8P .374" DR BARRIER,W  
/WASHERTE Part #826647-8  
8P AMPMODU II STIFT LEITE Part #1-1546119-2  
3PCR-08-006=3PCR ASSY

## Documents

### Product Drawings

[3PCR-11-006=3PCR ASSY](#)

English

### Datasheets & Catalog Pages

[1-1773458-2\\_BARRIER\\_STRIP\\_QUICK\\_REFERENCE\\_GUIDE](#)

English