


CUSTOMER DRAWING



Product Name	Product Dimensions			Cable Dimensions	
	L max	øA min	øB min	øD	øE ¹
D-607-10	24.0 (0.945)	4.0 (0.155)	2.8 (0.110)	1.8 to 4.0 (0.070 to 0.155)	1.9 to 2.8 (0.075 to 0.110)

1) Shield may be folded back over jacket to increase diameter.


MATERIALS

1. INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked polyvinylidene fluoride.
2. SOLDER PREFORM WITH FLUX:
SOLDER: TYPE Sn63 per ANSI-J-STD-006.
FLUX: TYPE ROL0 per ANSI-J-STD-004.
3. TERMINATOR BODY BASE METAL: Copper alloy.
Plating: Tin lead solder per SAE Specification AMS-P-81728.

APPLICATION

1. These parts are designed to provide an environment protected shield termination on cables, rated for 125°C minimum, meeting the dimensional criteria listed, having tin, or silver-plated copper shields.
2. Temperature range: -55°C to +150°C. Install using TE Connectivity approved convection or infrared tools in accordance with TE Connectivity assembly procedure ES-61139.

For best results, prepare the cable as shown:



 TE Connectivity		Raychem Devices		TITLE : PCB TERMINATOR				
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCHES DIMENSIONS ARE BETWEEN BRACKETS.				DOCUMENT NO.: D-607-10				
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ANGLES: N/A ROUGHNESS IN MICRON	TE Connectivity reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.		DOCUMENT REVISION: J		REVISION ISSUE DATE: 12-MAR-2020		
DRAWN BY: M. FORONDA		DATE: 24-AUG-1999	CAGE CODE: 06090	ECO NUMBER: ECO-20-003669		SCALE: None	SIZE: A	SHEET: 1 of 1