




P.C.B. LAYOUT






| ▲ SWITCH FUNCTION |        |          |
|-------------------|--------|----------|
| POS. 1            | POS. 2 | POS. 3   |
|                   |        |          |
| ON                | NONE   | ON       |
| 2-3, 5-6          | N/A    | 2-1, 5-4 |



CIRCUIT: DPDT

## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. PLATING MATERIAL: SILVER
5. RATING: 2 AMPS @250VAC  
5 AMPS @120VAC OR 28VDC
6. ELECTRICAL LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
8. DIELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL
9. OPERATING TEMP.: -30°C to 85°C
10. ▲ DENOTES CRITICAL PARAMETER.

▲ ACTUATOR  
COLOR: WHITE

| REV | ECO NO     | DESCRIPTION | DATE     | BY | E-SWITCH®             |                 |       |             | OBJECT ID |
|-----|------------|-------------|----------|----|-----------------------|-----------------|-------|-------------|-----------|
| A   | ECO-101324 | Release     | 10/19/22 | MW | TITLE 300DP1J1WHTM7QE |                 |       |             | 100122888 |
|     |            |             |          |    | SCALE 2:1             | DATE 10/17/2022 | DR MW | DWG T321087 | REV A     |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO  
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED