





REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₀	RELEASED	12/21/93	<i>DCmel</i>



RECOMMENDED MOUNTING HOLE

HOUSING CLAMP NUT MOUNTING NUT LOCKWASHER	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	PASSIVATE PER ASTM A380
SLEEVE	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
DIELECTRIC	NYLON	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, COND H	GOLD PLATE PER MIL-G-45204 OVER COPPER PLATE PER MIL-C-14550
FERRULE	SOFT COPPER ALLOY	GOLD PLATE PER MIL-G-45204
O-RING	SILICONE RUBBER PER ZZ-R-765	N/A
COMPONENT	MATERIAL	FINISH

CABLE ENTRY DIAMETER MINIMUM		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON		DRAWN BY <i>DCmel</i> DATE 12/21/93		AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599	
FERRULE	.099	FRAC.	DEC.	ANGLES	CHECKED BY		
SLEEVE	.036	± 1/64	± .005	± °	APPD BY <i>DCmel</i> 12/21/93	AMP	
DIELECTRIC	.021	These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.		USE ASS'Y PROCEDURE		TITLE SMA BULKHEAD FEEDTHRU CABLE JACK SOLDER ATTACH. M39012/59-3006 CAT.A	
CONTACT	.021			408-04925 (20-536)		SIZE B	CODE IDENT NO. 26805
				NO. AP.		2034-8006-92	REV 01 ₀
						SCALE 5:1	SHEET 1 OF 1

- NOTES:
- DESIGNED FOR USE WITH
RG-178/U CABLE
 - CAPTURED CENTER CONTACT