





NOTES:

- 1 FOR USE ON MINIATURE APPLICATORS (LEFT-RIGHT FEED)
- 2 HANDTOOL 180319 TO BE USED.
- 3 APPLICATION SPEC. 114-19025.
- 4 PRODUCT SPEC. 108-19084.
- 5 REVERSE REELED FOR MINI APPLICATOR.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



WIRE RANGE :
1,0 - 2,5 mm²
INSULATION RANGE :
2,5 - 3,8 mm DIA.

100689-4	TINPLATED	PH.BRONZE	1-100645-4
100689-3	UNPLATED	PH.BRONZE	1-100645-3
100689-2	TINPLATED	BRASS	1-100645-2
100689-1	UNPLATED	BRASS	1-100645-1
100689-4	TINPLATED	PH.BRONZE	100645-4
100689-3	UNPLATED	PH.BRONZE	100645-3
100689-2	TINPLATED	BRASS	100645-2
100689-1	UNPLATED	BRASS	100645-1

LOOSE PIECE		FINISH			MATERIAL	PARTNUMBER
—	—	—	—	—	CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED	
—	—	—	—	—	© COPYRIGHT 19 - BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED.AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.	
—	—	—	—	—	THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION ,19	
B1	REVISED PER ECO-09-020932	KK	AEG	27AUG09	AMP HOLLAND B.V. 's-Hertogenbosch, The Netherlands.	
B	EH-0935-93	P.B.	P.B.	03.12.93	NAME	
A	EH-0242-93	P.B.	P.B.	14.04.93	LOW INSERTION FORCE FASTON RECEPTACLE FOR 0,8 mm TABTHICKNESS .250srs(6,3)	
0	H-9565	P.B.	A.B.	20.02.92		
LTR.	REVISION RECORD	DR.	CHK.	DATE		

DR.: P.BEIJNON	CHK.: A.BIJNEN	APP.: L.v.SOEST.	DWG.No. C-100645	REV.LTR. B1	SHEET 1 OF 1	A3
DATE: 20.02.92	DATE: -	DATE: -				