IXYS

Polar™ HiPerFET™ Power MOSFET

IXFT88N30P
IXFH88N30P
IXFK88N30P

V_{DSS} = 300V
I_{D25} = 88A
$R_{DS(on)}$ ≤ 40mΩ
t_{rr} ≤ 200ns

N-Channel Enhancement Mode
Avalanche Rated
Fast Intrinsic Diode



TO-268 (IXFT)



TO-247(IXFH)



TO-264 (IXFK)



G = Gate D = Drain
S = Source Tab = Drain

Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 150°C	300	V
V_{DGR}	T_J = 25°C to 150°C, R_{GS} = 1MΩ	300	V
V_{GSS}	Continuous	± 20	V
V_{GSM}	Transient	± 30	V
I_{D25}	T_C = 25°C	88	A
$I_{L(RMS)}$	External Lead Current Limit	75	A
I_{DM}	T_C = 25°C, Pulse Width Limited by T_{JM}	220	A
I_A	T_C = 25°C	60	A
E_{AS}	T_C = 25°C	2	J
dV/dt	$I_S \le I_{DM}$, $V_{DD} \le V_{DSS}$, $T_J \le 150°C$	10	V/ns
P_D	T_C = 25°C	600	W
T_J		-55 to +150	°C
T_{JM}		+150	°C
T_{stg}		-55 to +150	°C
T_L	1.6mm (0.063in) from Case for 10s	300	°C
T_{SOLD}	Plastic Body for 10s	260	°C
M_d	Mounting Torque (TO-247&TO-264)	1.13/10	Nm/lb.in.
Weight	TO-268	4	g
	TO-247	6	g
	TO-264	10	g

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0V, I_D = 250μA	300			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 4mA	2.5		5.0	V
I_{GSS}	V_{GS} = ± 20V, V_{DS} = 0V			±100	nA
I_{DSS}	$V_{DS} = V_{DSS}$, V_{GS} = 0V			25	μA
	T_J = 125°C			250	μA
$R_{DS(on)}$	V_{GS} = 10V, $I_D = 0.5 \bullet I_{D25}$, Note 1			40	mΩ

Features

- International Standard Packages
- Fast Intrinsic Diode
- Avalanche Rated
- Low $R_{DS(ON)}$ and Q_G
- Low Package Inductance

Advantages

- High Power Density
- Easy to Mount
- Space Savings

Applications

- DC-DC Coverters
- Battery Chargers
- Switch-Mode and Resonant-Mode Power Supplies
- DC Choppers
- AC and DC Motor Drives
- Uninterrupted Power Supplies
- High Speed Power Switching Applications

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	V_{DS} = 10V, I_D = 0.5 • I_{D25}, Note 1	40	60		S
C_{iss}	V_{GS} = 0V, V_{DS} = 25V, f = 1MHz		6300		pF
C_{oss}			950		pF
C_{rss}			190		pF
$t_{d(on)}$	**Resistive Switching Times**		25		ns
t_r	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 60A		24		ns
$t_{d(off)}$	R_G = 3.3Ω (External)		96		ns
t_f			25		ns
$Q_{g(on)}$	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25}		180		nC
Q_{gs}			44		nC
Q_{gd}			90		nC
R_{thJC}				0.21	°C/W
R_{thCS}	TO-247		0.21		°C/W
	TO-264		0.15		°C/W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
I_S	V_{GS} = 0V			88	A
I_{SM}	Repetitive, Pulse Width Limited by T_{JM}			220	A
V_{SD}	I_F = I_S, V_{GS} = 0V, Note 1			1.5	V
t_{rr}	I_F = 25A, -di/dt = 100A/μs,		100	200	ns
Q_{RM}	V_R = 100V, V_{GS} = 0V		0 .6		μC

Note 1. Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.

TO-264 (IXFK) Outline



Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.82	5.13	.190	.202
A1	2.54	2.89	.100	.114
A2	2.00	2.10	.079	.083
b	1.12	1.42	.044	.056
b1	2.39	2.69	.094	.106
b2	2.90	3.09	.114	.122
c	0.53	0.83	.021	.033
D	25.91	26.16	1.020	1.030
E	19.81	19.96	.780	.786
e	5.46 BSC		.215 BSC	
J	0.00	0.25	.000	.010
K	0.00	0.25	.000	.010
L	20.32	20.83	.800	.820
L1	2.29	2.59	.090	.102
P	3.17	3.66	.125	.144
Q	6.07	6.27	.239	.247
Q1	8.38	8.69	.330	.342
R	3.81	4.32	.150	.170
R1	1.78	2.29	.070	.090
S	6.04	6.30	.238	.248
T	1.57	1.83	.062	.072

TO-247 (IXFH) Outline



Terminals: 1 - Gate 2 - Drain
3 - Source Tab - Drain

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.7	5.3	.185	.209
A_1	2.2	2.54	.087	.102
A_2	2.2	2.6	.059	.098
b	1.0	1.4	.040	.055
b_1	1.65	2.13	.065	.084
b_2	2.87	3.12	.113	.123
C	.4	.8	.016	.031
D	20.80	21.46	.819	.845
E	15.75	16.26	.610	.640
e	5.20	5.72	0.205	0.225
L	19.81	20.32	.780	.800
L1		4.50		.177
ØP	3.55	3.65	.140	.144
Q	5.89	6.40	0.232	0.252
R	4.32	5.49	.170	.216
S	6.15 BSC		242 BSC	

TO-268 (IXFT) Outline



SYM	INCHES MIN	MAX	MILLIMETERS MIN	MAX
A	.193	.201	4.90	5.10
A1	.106	.114	2.70	2.90
A2	.001	.010	0.02	0.25
b	.045	.057	1.15	1.45
b2	.075	.083	1.90	2.10
C	.016	.026	0.40	0.65
C2	.057	.063	1.45	1.60
D	.543	.551	13.80	14.00
D1	.488	.500	12.40	12.70
E	.624	.632	15.85	16.05
E1	.524	.535	13.30	13.60
e	.215 BSC		5.45 BSC	
H	.736	.752	18.70	19.10
L	.094	.106	2.40	2.70
L1	.047	.055	1.20	1.40
L2	.039	.045	1.00	1.15
L3	.010 BSC		0.25 BSC	
L4	.150	.161	3.80	4.10

Fig. 1. Output Characteristics @ T_J = 25ºC



Fig. 2. Extended Output Characteristics @ T_J = 25ºC



Fig. 3. Output Characteristics @ T_J = 125ºC



Fig. 4. $R_{DS(on)}$ Normalized to I_D = 44A Value vs. Junction Temperature



Fig. 5. $R_{DS(on)}$ Normalized to I_D = 44A Value vs. Drain Current



Fig. 6. Maximum Drain Current vs. Case Temperature



Fig. 7. Input Admittance



Fig. 8. Transconductance



Fig. 9. Forward Voltage Drop of Intrinsic Diode



Fig. 10. Gate Charge



Fig. 11. Capacitance



Fig. 12. Forward-Bias Safe Operating Area



Fig. 13. Maximum Transient Thermal Impedance