







POLE	2	3	4	5	6
A	7.80	11.30	14.80	18.30	21.80
B	3.50	7.00	10.50	14.00	17.50
Tol.	±0.10				

SIGN	DATE	DESCRIPTION	APPROVER
△	12/02'08	Flange screw changed from "-" to "+/-"	Tony
△	09/05/25	wire strip length changed from 6-7mm to 8-9mm	Eris
△	09/05/25	Withstanding Voltage changed from 1.3KV to 1.6KV	Eris
△	09/05/25	Add Safety Approval	Eris
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Terminal lever: Thermoplastic (UL94V-0)
- Item ② Terminal up housing: Thermoplastic (UL94V-0)
- Item ③ Wire guard: Stainless steel
- Item ④ Contact pin: PhBz (CuSn) , Tin plated.
- Item ⑤ With flange screw: M2.5 Steel Zinc plated.
- Item ⑥ Terminal down housing: Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating: 300 V
- Current rating: 8 A
- Wire range:
- Solid wire(AWG): 16-28
- Stranded wire(AWG): 16-28
- △ ● Wire strip length: 8-9 mm
- △ ● Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C

△ ● Safety Approval:

HW xx 1 0 x 2 xxxx G

No. OF POLES

02: 2 POLES

:

06: 6 POLES

COLOR

0: BLACK

5: GREEN (RAL 6018/T)

6: BLUE

8: GREY (RAL 7004/P)

G: Pb<40000ppm

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark

Any special item by customer request. please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HW 3.5mm W/Flange Series (2P-6P)					
PART NO.	HWxx10x2xxxxG			DWG NO.	8HW0403	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		
		Kind 2010.01.07	Eris 2009.05.25		UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30
					REVISION: D	X.XX ±0.10
SHEET: 01/01						X° ±1°

SIGN	DATE	DESCRIPTION	APPROVER
△	12/02'08	Flange screw changed from "-" to "+/-"	Tony
△	09/05/25	wire strip length changed from 6-7mm to 8-9mm	Eris
△	09/05/25	Withstanding Voltage changed from 1.3KV to 1.6KV	Eris
△	09/05/25	Add Safety Approval	Eris
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Terminal lever: Thermoplastic (UL94V-0)
- Item ② Terminal up housing: Thermoplastic (UL94V-0)
- Item ③ Wire guard: Stainless steel
- Item ④ Contact pin: PhBz.(CuSn) , Tin plated.
- Item ⑤ With flange screw: M2.5 Steel Zinc plated.
- Item ⑥ Terminal down housing: Thermoplastic (UL94V-0)

Electrical: cULus

● Voltage rating: 300 V

● Current rating: 8 A

● Wire range:

● Solid wire(AWG): 16-28

● Stranded wire(AWG): 16-28

△ ● Wire strip length: 8-9 mm

△ ● Withstanding Voltage: 1.6 KV

● Operating temperature: -40°C to +115°C

△ ● Safety Approval: 

HW xx 1 0 x 2 xxxx G

No. OF POLES

07: 7 POLES

:

:

24: 24 POLES

COLOR

0: BLACK

5: GREEN (RAL 6018/T)

6: BLUE

8: GREY (RAL 7004/P)

G: Pb<40000ppm

0000: "@" Logo (Standard)


000A: "ANYTEK" Mark





Any special item by customer request. please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HW 3.5mm W/Flange Series (7P-24P)						
PART NO.	HWxx10x2xxxxG			DWG NO.	8HW0401		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Kind 2010.01.07	Eris 2009.05.25		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
				SHEET: 01/01		REV.: D	X.XX ±0.10
						X° ±1°	



POLE		2	3	4	5	6	7	8	9	10	11	12
A							25.30	28.80	32.30	35.80	39.30	42.80
B							21.00	24.50	28.00	31.50	35.00	38.50
Tol.							±0.15					
POLE	13	14	15	16	17	18	19	20	21	22	23	24
A	46.30	49.80	53.30	56.80	60.30	63.80	67.30	70.80	74.30	77.80	81.30	84.80
B	42.00	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50
Tol.	±0.20						±0.30					