






N=Number of poles

Dim L	$(N-1) \times 3.50 + 4.9$
Dim B	$(N-1) \times 3.50$
Dim D	$(N-1) \times 3.50$

Poles	Dim B & Dim D	Dim L
2p	± 0.10	± 0.15
3p-6p	± 0.15	± 0.15
7p-12p	± 0.20	± 0.20
13p-16p	± 0.30	± 0.30



SECTION P-P

SIGN	DATE	DESCRIPTION	APPROVER
Δ			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ③ Male contact pin: Copper , Bright Tin plated over Nickel plated
- Item ④ Terminalhousing): LCP (UL94V-0)
- Item ⑤ Cover: LCP (UL94V-0)

Electrical: cULus

- Voltage rating: 300V
- Current rating: 10A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -45°C to $+130^{\circ}\text{C}$
- Reflow soldering temperature: $260^{\circ}\text{C}/10$ Sec max
- Safety Approval: cULus


OQ xx 1 G x 0 Bxxx G

No. OF POLES
02: 2 POLES
03: 3 POLES
...
16: 16 POLES

0 Black (RAL9005)

G RoHS compliant
(lead<4%)
In copper Alloy

B000: "@" Logo (Standard)
B00A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.



Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	OQ 3.50mm 180° Series 2P-16P Close THR						
PART NO.	OQxx1Gx0BxxxG			DWG NO.	80Q0C28		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		CHENMING 10/22-16	CHENMING 10/22-16		UNIT: mm		X. ± 0.50
					SCALE: NONE		X.X ± 0.30
					SHEET: 01/01		X.XX ± 0.10
					REV.: B		X° $\pm 1^{\circ}$