



LOG	DIST	REV	DESCRIPTION	DATE	APP
6	14				
			REVISED PER 0720-0230-93		

METRIC
DIMENSIONS LISTED IN mm [INCHES]

WIRE RANGE	E13288 Listed
22-16 AWG STRAINED	22-16 AWG STRAINED

LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

1 STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928, COMMERCIAL WIRE RANGE IS 22-16



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS
FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS
FOR APPLICATION
TOOLING INFORMATION
FOR ORDER ENTRY

MAX RECOMMENDED OPERATING
TEMPERATURE: 170°C MAX
VOLTAGE RATING:
NOT APPLICABLE
WIRE CROSS SECTIONAL AREA RANGE:
0.26-1.65mm² [509-3,260] CIR MILS
STRAINED
THIS DRAWING IS A CONTROLLING DOCUMENT FOR
THE CONSTRUCTION OF THE PART AND THE
CONSTRUCTION OF THE PART SHOULD BE
CONSISTENT WITH THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC # -
3 PLC DEC # -
ANGLES
MATERIAL
COPPER PER
ASTM B-152
ANNEALED
FINISH
TIN PLATE
0.00254 [0.000100] MIN
THK PER MIL-T-10727

DR 2-4-93
TA BRINKMAN
CHK 2-4-93
DA PATTERSON
APPO 2-4-93
DE MILLER
PRODUCT SPEC
APPLICATION SPEC
WEIGHT

AMP Incorporated
Harrisburg, PA 17105-3508
TERMINAL, RING TONGUE,
BUDGET
NAME
SIZE
CAGE CODE
DRAWING NO
SCALE
8:1
SHEET
1 OF 1