

DO NOT
SCALE FROM
THIS PRINT






FIG 1



CLE-1XX-XX-X-DV-XX

No OF POSITIONS
-04 THRU -90
(PER ROW)

LEAD STYLE
-01
(USE C-80-01-X)


PLATING SPECIFICATION
-F: 3μ" FLASH SELECTIVE GOLD
ON ENTIRE
CONTACT
-G: 10μ" LIGHT GOLD ON ENTIRE
CONTACT

OPTION


-P: PICK & PLACE PAD (SEE FIG 2, SHT 2)
(AVAILABLE ON POSITIONS -08 THRU -90 ONLY))
(USE LMP-10)
-TR: TAPE & REEL PACKAGING
-A: ALIGNMENT PIN (SEE FIG 3 & 4, SHT 2)
(MOLDED TO POSITION OR STAKED)
(SAMTEC DISCRETION WHICH -A PIN IS USED)
(STAKE 7 POSITIONS MIN)
(MOLD 4 POSITION MIN)
-K: POLYIMIDE FILM PAD
(AVAILABLE ON POS. 8 THRU 90 ONLY)
(SEE FIG 5, SHT 2)
(USE K-DOT-.157-.250-.005)

ROW SPECIFICATION
-D: DOUBLE ROW - VERTICAL
(USE CLE-90-D)

END WALLS TO BE
SYMMETRICAL ±.0050



DETAIL 'B'
SCALE 10:1



SECTION "A"-"A"

SEE NOTE 6	.004[.10]	POS. 04-65
	.006[.15]	POS. 66-90

NOTES:

1. REPRESENTS A CRITICAL DIMENSION.
2. NOTE DELETED.
3. MINIMUM PUSHOUT FORCE: .5 LB.
4. WILL LOSE TWO POSITIONS FOR EVERY CUT MADE. MAXIMUM CUT FLASH TO BE .010 [.25] WITH NO FLASH IN HOLES OR EXTENDING BELOW LEADS.
5. NOTE DELETED.
6. BURR ALLOWANCE: .003 [.08] MAX
7. ENDWALL AFTER CUTTING: .0115±.0025 [.292±.064]
8. VOIDS ON TOP SURFACE TO BE LOCATED AT VENDOR DISCRETION TO CONTROL PART WARPAGE.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS ANGLES
.XX: ±.01 [.3] 2°
.XXX: ±.005 [.13]
.XXXX: ±.0020 [.051]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 5:1

INSULATOR: LCP, UL 94 VO, COLOR: BLACK

CONTACT: BeCu 190 ALLOY [TM04]
THICKNESS: .007[.18]REF

DESCRIPTION:

.8MM x 1.2MM C.L. SOCKET STRIP ASSEMBLY

DWG. NO.

CLE-1XX-XX-X-DV-XX

BY: PURVIS 10/23/95

SHEET 1 OF 2




FIG 2
-P OPTION
8 POSITIONS MIN





FIG 5
-K: POLYIMIDE FILM PAD
8 POSITIONS MIN



NOTE: "R" = USED MEASURED DIMENSION (REF)
"S" = [("R" - .1575 [4.00]) / 2] ±.020 [.51]




FIG 3
-A STAKED OPTION
7 POSITIONS MIN






FIG 4
-A OPTION (MOLDED)
4 POSITIONS MIN

PACKAGING VIEW



PT-1-24-03-43
TP-24



PT-1-24-01-62
TP-12

FOR CLE-104/105-01-X-DV &
CLE-104/105-01-X-DV-A

ALL OTHER POSITIONS AND OPTIONS

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 5:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:
.8MM x 1.2MM C.L. SOCKET STRIP ASSEMBLY

DWG. NO.
CLE-1XX-XX-X-DV-XX

BY: PURVIS 10/23/95 SHEET 2 OF 2