







SECTION J-J

1. PREFIX AND SUFFIX NUMBERS MUST MATCH THOSE ON PLUG ASSEMBLY FOR PARTS TO MATE.
2. POLYESTER, FLAME RETARDANT, UL 94V-0 RATED, GLASS FILLED, BLACK.
3. 3.81µm [.000150] MIN BRIGHT TIN OVER 1.27µm [.000050] MIN NICKEL.
4. 1.27µm [.000050] MIN GOLD ON MATING SURFACE FOR A LENGTH OF 2.54 [.100] MIN, 3.81µm [.000150] MIN MATTE TIN ON OPPOSITE END FOR A LENGTH OF 3.81 [.150] MIN, BOTH OVER 1.27µm [.000050] MIN NICKEL ON ENTIRE CONTACT.
5. NUMBERS 13, 14, 15, 16 OR LETTER P TO APPEAR ON LOWER RIGHT REAR OF HOUSING IN AREA INDICATED.
6. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.
7. DIMENSION INDICATES CONTACT MATING ZONE.
8. POINT OF PLATING MEASUREMENT.

	E	5-1761190-1
OBSOLETE	B	2-1761190-1
OBSOLETE	A	1-1761190-1
KEY I.D. LETTER		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER 26APR04	TE Connectivity	
DIMENSIONS: mm[INCHES]		CHK C. ROHDE 26APR04	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. WALMSLEY 26APR04	PRODUCT SPEC	
0 PLC ± -		108-2047		
1 PLC ± -		APPLICATION SPEC		
2 PLC ± -		114-2081		
3 PLC ± 0.38 [.015]		SIZE		
4 PLC ± -		CAGE CODE		
ANGLES ± -		DRAWING NO		
FINISH		RESTRICTED TO		
SHIELD: 3		A1 00779 1761190		
CONTACT: 4		CUSTOMER DRAWING		
SCALE 4:1		SHEET 1 OF 1 REV A		