

DO NOT
SCALE FROM
THIS PRINT





FIG 1
[FHP-10-02-X-S SHOWN]






FIG 2
-LC & -A OPTIONS
[-LC & -A OPTIONS ONLY AVAILABLE ON -02 LEAD STYLE]
(SAME AS FIG 1, UNLESS OTHERWISE STATED)

FHP-XX-XX-XX-S-XX-XX

No OF POSITIONS
-02 THRU -24
(PER ROW)
[SEE POSITIONAL FILL VIEW]

LEAD STYLE
-01: THROUGH HOLE
(USE C-130-03-X)
-02: SURFACE MOUNT
(USE C-130-04-X)

* = INTERNAL USE ONLY
NOT FOR SALE

*POLARIZATION
-02 THRU -06, -08, -10, -12, -13 & -14
(SEE TABLE 1 FOR AVAILABLE COMBINATIONS)
(SEE SHT 3, IN-PROCESS 1 POLARIZED FILL)
(SEE NOTE 12)


OPTION
-TR: TAPE & REEL PACKAGING
(T&R AVAILABLE FOR 2 THRU 18 POS)
(SEE NOTES 6 & 10)

OPTION
-LC: LOCKING CLIP (USE LC-05-TM)
(-02 LEAD STYLE ONLY, SEE NOTE 11)
-A: ALIGNMENT PIN (USE FHP-XX-S-A)
(SEE FIG 2) (-02 LEAD STYLE ONLY)
-K: POLYIMIDE FILM PAD
(SEE FIG 3, SHT. 2) (USE K-DOT-.256-.375-.005)
(-02 LEAD STYLE ONLY)
(AVAILABLE ON POSITIONS 2-24,
2-4 POSITIONS MUST BE IN -TR)

ROW SPECIFICATION
-S: SINGLE (USE FHP-XX-S)

PLATING SPECIFICATION
-T: MATTE TIN CONTACT AND TAIL (USE C-130-XX-T)
-TM: MATTE TIN CONTACT AND TAIL (USE C-130-XX-T)
-H: 30μ" GOLD IN CONTACT AREA,
3μ" GOLD ON TAIL (USE C-130-XX-H)

SECTION "A"- "A"
STYLE -02



NOTES:

STYLE -01

1. REPRESENTS A CRITICAL DIMENSION.
2. COPLANARITY TO BE WITHIN .006".
3. BURR ALLOWANCE: .0015 MAX.
4. MAXIMUM CUT FLASH: .020.
5. MINIMUM PUSHOUT FORCE: 1.0 LB.
6. LAYER PACKAGE STYLE -01 & -02, POSITIONS 02 - 04 WITH NO OPTIONS ONLY.
7. OPEN PART OF CONTACT FILLED TOWARDS #1 PIN INDICATOR
8. MINIMUM WALL THICKNESS TO BE .010".
9. MEASURED @ BEND.
10. TUBE PACKAGING AVAILABLE FOR 5 THRU 24 POSITIONS.
11. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION IS NOT COMPATIBLE WITH AUTO PLACEMENT. SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION.
12. POLARIZATION NUMBER INDICATES THE AMOUNT OF LIVE CONTACTS IN THE CONNECTOR.

TABLE 1

FINISHED GOODS	SUB ASSEMBLY
FHP-02-02-T-S-XX	FHP-24-02-T-S-02
FHP-02-01-T-S-XX	FHP-24-01-T-S-02
FHP-03-02-T-S-XX	FHP-24-02-T-S-03
FHP-04-01-T-S-XX	FHP-24-01-T-S-04
FHP-04-02-T-S-XX	FHP-24-02-T-S-04
FHP-05-02-T-S-XX	FHP-24-02-T-S-05
FHP-06-01-TM-S-XX / T-S-XX	FHP-24-01-T-S-06
FHP-08-01-T-S-XX	FHP-24-01-T-S-08
FHP-10-02-T-S-XX / TM-S-XX	FHP-24-02-T-S-10
FHP-12-02-T-S-XX	FHP-24-02-T-S-12
FHP-13-01-T-S-XX	FHP-24-01-T-S-13
FHP-14-01-T-S-XX	FHP-24-01-T-S-14
ALL REMAINING CONFIGURATIONS	FHP-24-XX-X-S

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS ANGLES
.XX: ±.01
.XXX: ±.005
.XXXX: ±.0020

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 1.5:1
MATERIAL: VECTRA E130i
COLOR: BLACK
CONTACT: BeCu, 174HT

F:\DWG\MISC\MKTG\FHP-XX-XX-S-XX-XX-MKT.SLDRW


samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
.156 HI POWER SOCKET ASSEMBLY


DWG. NO. FHP-XX-XX-XX-S-XX-XX-XX

BY: BRATCHER 03/01/99 SHEET 1 OF 3





NOTE: "M" = USED MEASURED DIMENSION (REF)
"P" = { ("M" - .256 [6.50]) / 2 } ± .020 [.51]


FIG 3
-K: POLYIMIDE FILM PAD OPTION
(SHOWN: FHP-10-02-X-S-K)




(TUBE PACKAGING AVAILABLE FOR 5 THRU 24 POS)
(TUBE PACKAGE THE PARTS WITH #1 PIN TOWARDS ARROW)

PACKAGING TABLE			
LEAD STYLE	OPTIONS	PACKAGING TUBE	PLUG
-01	ALL OPTIONS	PT-1-24-02-44	TP-03
-02	ALL OPTIONS	PT-1-24-02-44	TP-03




<p>• PROPRIETARY NOTE •</p> <p>THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.</p>		<p>F:\DWG\MISC\MKTG\FHP-XX-XX-XX-S-XX-XX-MKT.SLDDRW</p>  <p>520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322</p>	
DO NOT SCALE DRAWING		DESCRIPTION: .156 HI POWER SOCKET ASSEMBLY	
SHEET SCALE: 1:0.666667		DWG. NO. FHP-XX-XX-XX-S-XX-XX-XX	
		BY: BRATCHER	03/01/99 SHEET 2 OF 3


-02 POLARIZATION
(8 FINISHED GOODS)
FHP-24-02-XX-S-02 SHOWN




-03 POLARIZATION
(6 FINISHED GOODS)
FHP-24-02-XX-S-03 SHOWN



-04 POLARIZATION
(5 FINISHED GOODS)
FHP-24-02-XX-S-04 SHOWN



-05 POLARIZATION
(4 FINISHED GOODS)
FHP-24-02-XX-S-05 SHOWN




-06 POLARIZATION
(3 FINISHED GOODS)
FHP-24-01-XX-S-06 SHOWN




-08 POLARIZATION
(2 FINISHED GOODS)
FHP-24-01-XX-S-08 SHOWN



-10 POLARIZATION
(2 FINISHED GOODS)
FHP-24-02-XX-S-10 SHOWN




STANDARD FILL



4 POSITION SHOWN
[PRIOR TO CUT-TO-POSITION OPERATION]

-12 POLARIZATION
(1 FINISHED GOODS)
FHP-24-02-XX-S-12 SHOWN




-13 POLARIZATION
(1 FINISHED GOODS)
FHP-24-01-XX-S-13 SHOWN



-14 POLARIZATION
(1 FINISHED GOODS)
FHP-24-01-XX-S-14 SHOWN



* PROPRIETARY NOTE *		 520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322	
DO NOT SCALE DRAWING		DESCRIPTION: .156 HI POWER SOCKET ASSEMBLY	
SHEET SCALE: 1.25:1		DWG. NO. FHP-XX-XX-XX-S-XX-XX-XX	
		BY: BRATCHER	03/01/99 SHEET 3 OF 3