






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECO-14-000933	30JAN2014	AP	DD



- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.
4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- 5 FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH,
Ø3.66 DRILL, AND Ø6.5 PAD.
6. KEYING PIN SHOWN IN POSITION A, SEE KEYING CHART
ON SHEET 2 FOR OTHER POSITIONS.




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COELLO	02JUN2011	TE Connectivity	
DIMENSIONS:		CHK J. EABY	02JUN2011		
mm		APVD J. EABY	02JUN2011		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		NAME	
0 PLC ±		APPLICATION SPEC		IMPACT, 5 PAIR, 6 COLUMN, HEADER	
1 PLC ±0.25		WEIGHT		LEFT GUIDED, RIGHT END WALL	
2 PLC ±0.13		CUSTOMER DRAWING		SIGNAL MODULE, 0.39 PTH	
3 PLC ±		SCALE		SIZE	
4 PLC ±		SHEET		CAGE CODE	
ANGLES ±		REV		DRAWING NO	
FINISH		B		2143138	
SEE TABLE					

REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

	H	5.5	8-2143138-6
	H	4.9	8-2143138-5
	H	4.5	8-2143138-4
	H	5.5	8-2143138-3
	H	4.9	8-2143138-2
	H	4.5	8-2143138-1
	G	5.5	7-2143138-6
	G	4.9	7-2143138-5
	G	4.5	7-2143138-4
	G	5.5	7-2143138-3
	G	4.9	7-2143138-2
	G	4.5	7-2143138-1
	F	5.5	6-2143138-6
	F	4.9	6-2143138-5
	F	4.5	6-2143138-4
	F	5.5	6-2143138-3
	F	4.9	6-2143138-2
	F	4.5	6-2143138-1
	E	5.5	5-2143138-6
	E	4.9	5-2143138-5
	E	4.5	5-2143138-4
	E	5.5	5-2143138-3
	E	4.9	5-2143138-2
	E	4.5	5-2143138-1
	D	5.5	4-2143138-6
	D	4.9	4-2143138-5
	D	4.5	4-2143138-4
	D	5.5	4-2143138-3
	D	4.9	4-2143138-2
	D	4.5	4-2143138-1
	C	5.5	3-2143138-6
	C	4.9	3-2143138-5
	C	4.5	3-2143138-4
	C	5.5	3-2143138-3
	C	4.9	3-2143138-2
	C	4.5	3-2143138-1
	B	5.5	2-2143138-6
	B	4.9	2-2143138-5
	B	4.5	2-2143138-4
	B	5.5	2-2143138-3
	B	4.9	2-2143138-2
	B	4.5	2-2143138-1
	A	5.5	1-2143138-6
	A	4.9	1-2143138-5
	A	4.5	1-2143138-4
	A	5.5	1-2143138-3
	A	4.9	1-2143138-2
	A	4.5	1-2143138-1
	-	5.5	2143138-6
	-	4.9	2143138-5
	-	4.5	2143138-4
	-	5.5	2143138-3
	-	4.9	2143138-2
	-	4.5	2143138-1
FINISH	KEY POSITION	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY



THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R. COELLO	02JUN2011	 TE Connectivity			
			CHK J. EABY	02JUN2011				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME	IMPACT, 5 PAIR, 6 COLUMN, HEADER LEFT GUIDED, RIGHT END WALL SIGNAL MODULE, 0.39 PTH		
mm								
		0 PLC ± 1 PLC ±0.25 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±			PRODUCT SPEC -			
		APPLICATION SPEC -			WEIGHT -			
MATERIAL -		FINISH SEE TABLE			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
					A1	00779	C=2143138	-
CUSTOMER DRAWING					SCALE	5:1	SHEET	2 OF 2
							REV	B