

Frequency Mixer WIDE BAND

SIM-153LH+

Level 10 (LO Power +10 dBm) 3200 to 15000 MHz

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW

For extended temperature range, consult factory.
Permanent damage may occur if any of these limits are exceeded.

Pin Connections

LO	8
RF	4
IF	2
GROUND	1,3,5,6,7


Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F	G
.200	.180	.087	.025	.050	.028	.043
5.08	4.57	2.2098	0.64	1.27	0.71	1.09
H	J	K	L	M	N	wt
.050	.030	.043	.204	.127	0.065	grams
1.27	0.76	1.09	5.18	3.23	1.65	0.08

Demo Board MCL P/N: TB-458+ Suggested PCB Layout (PL-517)



NOTES:

1. TRACE WIDTH AND GAP ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .0028(.0015); COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
-

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- wide bandwidth, 3200 to 15000 MHz
- low conversion loss, 6.1 dB typ.
- high L-R isolation, 36 dB typ.
- excellent IF BW, DC to 4000 MHz
- LTCC double balanced mixer
- tiny size, low profile, 0.08"
- useable as up and down converter
- aqueous washable
- protected by US patent 7,027,795

Applications

- satellite up and down converters
- defense radar and communications
- line of sight links
- federal fixed service
- WIFI
- blue tooth
- VSAT
- ISM

Electrical Specifications

FREQUENCY (MHz)	CONVERSION LOSS* (dB)			LO-RF ISOLATION (dB)		LO-IF ISOLATION (dB)		IP3 at center band (dBm)
	Typ.	σ	Max.	Typ.	Min.	Typ.	Min.	
LO/RF f_L - f_U	IF							Typ.
3200-15000	DC-4000							
3200-4500	6.4	0.2	8.9	40	32	19	13	12
4500-5100	6.5	0.2	8.7	38	32	15	10	18
5100-14000	7.5	0.4	12.4	35	23	15	9	—
14000-15000	7.8	0.3	10.3	30	17	28	19	—


1 dB Compression: +3 dBm typ.

* Conversion loss at 30 MHz IF. σ is a measure of repeatability from unit to unit.

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +10dBm	LO +10dBm	LO +10dBm	LO +10dBm	LO +10dBm
3200.00	3231.00	6.79	40.99	20.99	2.37	13.77
4000.00	4031.00	6.14	40.60	18.67	3.17	5.31
4500.00	4531.00	6.20	36.96	15.28	2.55	3.13
5000.00	5031.00	6.53	39.95	13.46	3.80	1.69
5600.00	5631.00	6.82	38.66	14.05	3.82	2.42
6500.00	6531.00	5.78	39.33	16.94	2.37	2.99
7400.00	7431.00	5.18	35.38	16.21	1.28	3.04
8000.00	8031.00	5.34	27.64	11.48	1.59	2.38
8500.00	8531.00	5.64	28.80	15.40	2.21	1.70
9000.00	9031.00	6.60	41.06	22.55	3.22	1.81
9500.00	9531.00	7.58	32.65	20.12	3.61	2.04
10000.00	10031.00	8.06	35.87	19.69	4.59	2.89
11000.00	11031.00	8.79	42.06	28.67	5.03	2.72
12000.00	12031.00	9.65	35.00	41.07	5.08	2.82
12600.00	12631.00	9.68	35.75	40.20	5.15	2.00
13050.00	13081.00	9.86	38.27	36.10	4.51	1.87
13500.00	13531.00	9.68	37.53	33.24	4.42	2.32
14025.00	14056.00	8.42	37.98	30.91	2.53	2.74
14550.00	14581.00	7.32	32.13	29.55	1.16	2.43
15075.00	15106.00	8.42	24.21	30.95	1.92	2.93

Electrical Schematic



Generic photo used for illustration purposes only

CASE STYLE: HV1195









+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel
at no extra cost

Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200, 500



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

